

Han 1HC-sti-s-M10 350A



Part number	09 11 001 2655
Specification	Han 1HC-sti-s-M10 350A
HARTING eCatalogue	https://b2b.harting.com/09110012655
Identification	
Category	Inserts
Series	Han [®] HC Modular
Identification	350

Version

Termination method	Screw termination
Gender	Male
Details	Please ensure to hold up the contact with a wrench size 17 to apply the tightening torque

Technical characteristics

Conductor cross-section	≤120 mm²
Electrical data acc. to IEC 61984	350 A 2,000 V 12 kV 3
Rated current	350 A
Rated voltage	2,000 V
Rated impulse voltage	12 KV
Pollution degree	3
Insulation resistance	≥10 ¹⁰ Ω
Contact resistance	≤0.2 mΩ
Limiting temperature	-40 +125 °C
Tightening torque	14 Nm
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate Polyamide
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated

Page 1 / 2 | Creation date 2018-09-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	265.5 g
Country of origin	Germany
Customs tariff number	85359000