

Han B Hood HC 4 Pegs - no openings



Part number	09 30 016 0801
Specification	Han B Hood HC 4 Pegs - no openings
HARTING eCatalogue	https://b2b.harting.com/09300160801

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hoods
Type	High construction

Version

Locking type	Double locking lever
Size	16 B
Version	Without cable entry
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	230.2 g
Country of origin	Germany
Customs tariff number	85389099