


## Han K 3/0 Pos. male Insert Screw Term.



Part number	09 38 005 2622
Specification	Han K 3/0 Pos. male Insert Screw Term.
HARTING eCatalogue	<a href="https://b2b.harting.com/09380052622">https://b2b.harting.com/09380052622</a>

### Identification

Category	Inserts
Series	Han-Com®
Identification	Han® K 3/0
Specification	Angled

### Version

Termination method	Axial screw termination
Gender	Male
Size	24 B
Number of contacts	3

### Technical characteristics

Conductor cross-section	35 ... 70 mm²
Electrical data acc. to IEC 61984	200 A 1,150/2,000 V 8 kV 3
Rated current	200 A
Rated voltage conductor-earth	1,150 V
Rated voltage conductor-conductor	2,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current acc. to UL	200 A
Rated voltage acc. to UL	600 V
Rated current acc. to CSA	160 A
Rated voltage acc. to CSA	600 V
Insulation resistance	≥10 <sup>10</sup> Ω
Contact resistance	≤0.2 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	22 mm
Tightening torque	8 Nm @ 35 mm² 9 Nm @ 50 mm²



Pushing Performance

## Technical characteristics

	10 Nm @ 70 mm <sup>2</sup>
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	402.06 g
Country of origin	Germany
Customs tariff number	85366990