

Han 3A Hood Angled Entry M20



Part number	19 20 003 1643
Specification	Han 3A Hood Angled Entry M20
HARTING eCatalogue	https://b2b.harting.com/19200031643

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hoods
Description of hood/housing	for Han-Brid® With glued seal

Version

Locking type	Single locking lever
Size	3 A
Version	Side entry
Cable gland	1x M20
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
----------------	----

Net weight	81 g
------------	------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------
