

Han 32A-gg-QB-M32



Part number	19 20 032 0437
Specification	Han 32A-gg-QB-M32
HARTING eCatalogue	https://b2b.harting.com/19200320437

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hoods
Type	High construction

Version

Locking type	Double locking lever (on the hood)
Han-Easy Lock®	Yes
Size	32 A
Version	Top entry
Cable entry	1x M32
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	263 g
Country of origin	Germany
Customs tariff number	85389099