

Han High Density module, crimp male



Part number	09 14 025 3001
Specification	Han High Density module, crimp male
HARTING eCatalogue	https://b2b.harting.com/09140253001

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] High Density module

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	25
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 0.52 mm²
Electrical data acc. to IEC 61984	4 A 50 V 0.8 kV 3
Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	≥10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	2
Net weight	8.12 g
Country of origin	Germany
Customs tariff number	85389099