

## Han 10HPR Hood Side Entry M32 Screw lock



Part number	19 40 010 0512
Specification	Han 10HPR Hood Side Entry M32 Screw lock
HARTING eCatalogue	<a href="https://b2b.harting.com/19400100512">https://b2b.harting.com/19400100512</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Hoods

### Version

Locking type	Screw locking
Size	10 B
Version	Side entry
Cable gland	1x M32
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

## Material properties

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076  
CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size 1

Net weight 470.33 g

Country of origin Germany

Customs tariff number 85389099