



#### Polyamide Spiral Binding for added strength and protection against abrasion

##### SBPA

SBPA spiral binding is used for cable harnesses in the automobile industry and for many demanding industrial applications.


##### Features and Benefits

- Organises and protects cables and hoses
- Very good protection against abrasion
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters and colours



SPBA spiral binding made of polyamide offers excellent protection against abrasion.

<b>MATERIAL</b>	Polyamide 6 (PA6)
<b>Operating Temperature</b>	-60 °C to +95 °C, intermittent +130 °C
<b>Flammability</b>	UL94 HB



Spiral binding

TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPA1.5	1.5	0.40	6.0	1.6	8.0	Natural (NA)	30 m	161-42000
SBPA4	4	0.60	7.8	5.0	20.0	Natural (NA)	30 m	161-42100
SBPA9	9	1.00	12.5	10.0	100.0	Natural (NA)	30 m	161-42200
SBPA16	16	1.20	16.0	20.0	150.0	Natural (NA)	30 m	161-42300

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.