

Polyethylene Spiral Binding for enhanced flame protection

SBPEFR


The flame-retardant properties of SBPEFR make it suitable for applications in the automobile and electrical industries, where enhanced fire protection is needed.

Features and Benefits

- Organises and protects cables and hoses
- Self-extinguishing according to UL94 V2
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters and colours



Spiral binding SBPEFR is available in a wide range of diameters and in colours black and white.



MATERIAL	Polyethylene (PEFR), Flame retardant
Operating Temperature	-60 °C to +80 °C, intermittent +120 °C
Flammability	UL94 V2, FMVSS 302, Type B



TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPEFR1.5	1.5	0.80	6.0	1.6	8.0	Black (BK)	30 m	161-43001
	1.5	0.80	6.0	1.6	8.0	White (WH)	30 m	161-43000
SBPEFR4	4	1.00	7.8	5.0	20.0	Black (BK)	30 m	161-43101
	4	1.00	7.8	5.0	20.0	White (WH)	30 m	161-43100
SBPEFR9	9	1.40	12.5	10.0	100.0	Black (BK)	30 m	161-43201
	9	1.40	12.5	10.0	100.0	White (WH)	30 m	161-43200
SBPEFR16	16	1.60	16.0	20.0	150.0	Black (BK)	30 m	161-43301
	16	1.60	16.0	20.0	150.0	White (WH)	30 m	161-43300

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.