

## Han Q 8/0-asw-16



Part number	09 12 008 0901
Specification	Han Q 8/0-asw-16
HARTING eCatalogue	<a href="https://b2b.harting.com/09120080901">https://b2b.harting.com/09120080901</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Surface mounted housing
Description of hood/housing	for Han-Compact® half cable gland

### Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Angled entry
Cable entry	1x Pg 16
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Polyamide
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	10
Net weight	30.3 g
Country of origin	Germany
Customs tariff number	85389099