

## Han Yellock 30HSM 2xM25 with bulkhead h.



Part number	11 12 300 1215
Specification	Han Yellock 30HSM 2xM25 with bulkhead h.
HARTING eCatalogue	<a href="https://b2b.harting.com/11123001215">https://b2b.harting.com/11123001215</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Surface mounted housing
Description of hood/housing	incl. bulkhead mounted housings

### Version

Locking type	Screw locking
Size	Han-Yellock® 30
Version	Side entry
Cable entry	2x M25
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Specifications EN 60664-1  
IEC 61984

Approvals DNV GL

## Commercial data

Packaging size 1

Net weight 519 g

Country of origin China

Customs tariff number 85389099