



### Manual Tensioning Tool for KR-Series

#### KR6/8

Application tool KR6/8 crimps the glass-fibre-reinforced locking pin of the KR seal and leads to plastic deformation of the tie ends. This produces a very permanent connection.

#### Features and Benefits

- Tough metal tool
- For applying KR-cable ties only
- For tensioning, fixing and cutting KR-cable ties
- Simply change the front plate to apply two different strap widths: 6 mm and 8 mm



KR6/8.

TYPE	For Ties	Strap Width max.	Weight	Article-No.
KR6/8	KR6, KR8	8.0	0.52 kg	121-00680
SP KR6/8 replacement blade	KR6, KR8	-	0.01 kg	122-68019

All dimensions in mm. Subject to technical changes.

### Pneumatic Tensioning Tool for KR-Series

#### KR8PNSE

Application tool KR8PNSE crimps the glass-fibre-reinforced locking pin of the KR seal and leads to plastic deformation of the tie ends. This produces a very permanent connection.

#### Features and Benefits

- Tough metal tool
- Pneumatic
- For applying KR-cable ties only
- For tensioning, fixing and automatically cutting KR-cable ties
- Tensioning force can be adapted with the air pressure
- Holding ring for a balancer



KR8PNSE.

<b>Air Supply</b>	Non oiled / oiled
<b>Air Pressure (min.)</b>	3 Bar
<b>Air Pressure (max.)</b>	4 Bar
<b>Hose Internal Diameter</b>	6.0 mm
<b>L x H x W</b>	approx. 320 x 210 x 50 mm
<b>Specifications</b>	CE, GS

RoHS

TYPE	For Ties	Strap Width max.	Weight	Article-No.
KR8PNSE	KR8	8.0	1.56 kg	121-00889
SP KR8PNSE replacement blade	KR8	-	0.01 kg	122-80032

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.