



## Warehouse and pipe labelling, thermal transfer

### Helatag 1213

Identification of storage systems with barcode and location information. Coloured labels for general marking of parts and components, samples and blocked goods in quality assurance, storage boxes and barrels.


The specially formulated adhesive labels give the highest quality print clarity when printed on thermal transfer printers. The range of materials and ribbons have been developed to suit the needs of most users. Designing and printing labels is simple and users can quickly print out professional labels in a matter of moments when using TagPrint Pro labelling software.

#### Features and Benefits

- Pipe, warehouse and shelving label
- Supplied on a continuous roll and cut by hand or automated with printer cutters
- Excellent print performance using TT822OUT ribbon
- Print with TT4000+, TT430 for best results
- Easy label design with TagPrint Pro



Large and highly visible pipe marking.



|                                  |                                                                                                           |
|----------------------------------|-----------------------------------------------------------------------------------------------------------|
| <b>MATERIAL</b>                  | Type 1213, Vinyl (PVC), glossy colours                                                                    |
| <b>Operating Temperature</b>     | -40 °C to +90 °C                                                                                          |
| <b>Curing Temperature</b>        | from +8 °C                                                                                                |
| <b>Adhesive</b>                  | Acrylic                                                                                                   |
| <b>Thickness of Foil (µm)</b>    | 66 µm                                                                                                     |
| <b>Chem. Material Properties</b> | Resistant to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis. |
| <b>Recommended Ribbon Type</b>   | TT822OUT, TTRW                                                                                            |

RoHS



| TYPE              | Width (W) | Width of Liner (WL) | Pack Cont. | Colour              | Article-No. |
|-------------------|-----------|---------------------|------------|---------------------|-------------|
| TAGR4TD1-1213-YE  | 25.0      | 25.0                | 50 m       | Yellow gloss (GSYE) | 596-03103   |
| TAG108TD1-1213-BU | 40.0      | 40.0                | 50 m       | Blue (BU)           | 596-12181   |
| TAG108TD1-1213-GN | 40.0      | 40.0                | 50 m       | Green (GN)          | 596-12166   |
| TAG108TD1-1213-YE | 40.0      | 40.0                | 50 m       | Yellow gloss (GSYE) | 596-12167   |
| TAGR1TD-1213-GN   | 101.6     | 101.6               | 50 m       | Green (GN)          | 596-12170   |
| TAGR1TD-1213-RD   | 101.6     | 101.6               | 50 m       | Red (RD)            | 596-12168   |
| TAGR1TD-1213-WH   | 101.6     | 101.6               | 50 m       | White (WH)          | 596-12171   |
| TAGR1TD-1213-YE   | 101.6     | 101.6               | 50 m       | Yellow gloss (GSYE) | 596-12169   |

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.