

CK P1




CK P2



CK P4



CK Y1



CK Y4

CK P1 · CK P2 · CK P4
Miniature load cell made of aluminium

Technical data

- High level of accuracy
- Comprehensive error
  CK P1 / CK P2: 0,03 %
  CK P4: 0,05 %
- Protection against dust and water splashes IP65 (in accordance with EN 60529)
- Aluminium
- Suitable for small scales and kitchen scales and force-measuring devices
- Cable length: 0,25 m

CK Y1 · CK Y4
Flat miniature alloy steel load cell

Technical data

- Accuracy in accordance with OIML C1
- RoHS compliant
- High precision
  (comprehensive Error 0,05 % F.S.)
- Very low design
- Ideal, for example, for the construction of personal floor scales, kitchen scales, postal scales or other scales with minimal structural height
- Cable length: 0,45 m

CK Y1

- Protection against dust and water splashes IP66
- Scope of delivery: 1 piece
- Full bridge circuit(junction box required to connect several measuring cells)

CK Y4

- Protection against dust and water splashes IP65
- Scope of delivery: 4 pieces
- Quarter bridge circuit: 4 weighing cells are connected to a full bridge
- No junction box necessary
- No corner adjustment

Discover more details and matching accessories online!

STANDARD



OPTION



STANDARD



CK Y4 CK Y1

Model	Nominal load
SAUTER	kg
CK 600-0P1	0,6
CK 1-0P1	1
CK 2-0P1	2
CK 3-0P1	3
CK 5-0P1	5
CK 6-0P1	6
CK 300-0P4	0,3
CK 500-0P4	0,5

Model	Nominal load
SAUTER	kg
CK 10-Y1	10
CK 30-Y1	30
CK 10-Y4	40
CK 30-Y4	120
CK 50-Y4	200