



TECHNICAL INFORMATION

Watts:	29
Lumens:	3480
Shape:	Square
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Aluminium + PMMA + PP
PF:	>0.9
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	120°
Color:	4000K
Dimension:	620x620x13mm
Output Voltage:	DC:30-42V

HIGH LUMEN 62X62 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6471 - 1563 940

[View more details](#)



FEATURES

- Powerful LED light source with lumen efficiency of 120LM/W LM/W
- Strong and sturdy Aluminium + PMMA + PP body
- Fitted with high efficiency SMD LED Chips
- Easy to connect driver for quicker installation
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 17.5
Unit CBM: 0.058212
Dimension: 620x620x13mm

MASTER BOX PACKAGING

Box Qty: 6

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157641012