

Snapper Hose Clips for Tubes and Harnesses

SNP-Series


SNP range may replace metal hose clamps. Snapper hose clips can be used in markets as diverse as automotive, agriculture, white goods, venting systems, pumps and hydraulic systems to medical engineering.

Features and Benefits


- Releasable and reusable plastic hose clamps
- Self-locking
- Releasable by giving a lateral movement to the 'head'
- Installation by hand possible
- Installation with processing tool for secure tensing
- For higher operating temperatures: Glass Filled PA66



SNP - Snapper Hose Clips range.



SNP - Snapper Hose Clip (front view)



SNP Clip (side view)

i SNP Snapper are also available on request in material PA66HS and PA46.

Snapper tools please see page 527.


TYPE	Bundle Ø min.	Bundle Ø max.	Width (W) min.	Width (W) max.	Width (W2)	Wall (WT)	Material	Colour	Article-No.
SNP1	6.0	6.5	8.33	11.73	3.8	1.00	POM	White (WH)	190-00022
	6.0	6.8	8.56	11.79	3.8	1.00	PA66GF13	Black (BK)	192-10010
SNP1.25	7.1	7.7	10.57	12.62	3.8	1.10	PA66GF13	Black (BK)	190-00029
SNP1.5	7.8	9.2	13.00	17.00	3.7	1.40	PA66GF15	Black (BK)	193-00150
SNP2(E)	8.7	10.0	17.00	21.00	6.0	1.50	POM	Natural (NA)	191-10029
SNP2	9.3	10.5	12.22	17.48	5.9	1.70	PA66GF13	Black (BK)	192-10020
SNP3(E)	10.0	11.4	19.00	25.00	6.0	1.80	POM	Natural (NA)	191-10039
SNP4	10.4	11.7	13.39	19.15	5.9	1.70	PA66GF13	Black (BK)	192-10040
SNP4(E)	10.8	12.3	19.00	23.00	6.0	1.80	POM	Natural (NA)	191-10049
SNP7	11.4	13.7	18.62	28.73	5.9	1.70	PA66GF13	Black (BK)	192-10070
SNP6	11.7	13.3	14.71	21.54	5.9	1.70	PA66GF13	Black (BK)	192-10060
SNP6(E)	12.0	13.7	19.00	24.00	6.0	1.80	POM	Natural (NA)	191-10069
SNP8	13.1	15.0	16.69	24.89	5.7	1.70	PA66GF13	Black (BK)	192-10080
SNP8(E)	13.7	15.3	19.00	24.00	6.0	1.80	POM	Natural (NA)	191-10089
SNP10	14.5	16.6	17.60	26.90	5.9	1.80	PA66GF13	Black (BK)	192-10100
SNP10(E)	15.0	16.8	19.00	24.00	6.0	1.80	POM	Natural (NA)	191-10109
SNP12A	15.9	18.2	20.96	29.90	5.9	1.80	PA66GF13	Black (BK)	190-00254
SNP12(E)	16.8	18.4	19.00	24.00	6.0	1.80	POM	Natural (NA)	191-10129
SNP14(E)	18.1	19.9	19.00	24.00	6.0	1.80	POM	Natural (NA)	191-10149
SNP14A	18.5	21.0	20.90	30.10	5.9	1.80	PA66GF13	Black (BK)	190-00300
SNP16	19.1	21.7	19.89	30.81	5.8	1.50	PA66GF13	Black (BK)	192-10160
SNP16(E)	19.9	21.7	19.00	24.00	6.0	1.90	POM	Natural (NA)	191-10169
SNP18A	20.0	23.1	24.03	35.51	5.9	1.80	PA66GF13	Black (BK)	190-00258
SNP18(E)	21.4	23.0	16.00	22.00	6.0	1.90	POM	Natural (NA)	191-10189
SNP19	22.3	25.3	22.30	36.09	5.9	1.80	PA66GF13	Black (BK)	190-00090

All dimensions in mm. Subject to technical changes.



Snapper Hose Clips for Tubes and Harnesses

SNP-Series



SNP - Snapper Hose Clip (front view)



SNP Clip (side view)



Material specification please see page 24.

TYPE	Bundle Ø min.	Bundle Ø max.	Width (W) min.	Width (W) max.	Width (W2)	Wall (WT)	Material	Colour	Article-No.
SNP20(E)	22.7	24.7	20.00	26.00	6.0	1.80	POM	Natural (NA)	191-10209
SNP22	23.7	27.4	23.90	37.69	6.0	1.80	PA66GF13	Black (BK)	192-10220
SNP22(E)	25.3	27.3	20.00	26.00	6.0	1.60	POM	Natural (NA)	191-10229
SNP24	25.8	29.2	26.49	39.40	7.4	1.70	PA66GF13	Black (BK)	192-10240
SNP24(E)	26.5	28.6	26.50	39.40	7.4	2.50	POM	Natural (NA)	191-10249
SNP28	29.1	33.6	25.91	41.81	7.3	1.70	PA66GF13	Black (BK)	190-00127
SNP32(E)	30.3	33.1	27.00	34.00	7.5	2.00	POM	Natural (NA)	191-10329
SNP32	31.2	35.8	27.33	44.40	7.3	1.80	PA66GF13	Black (BK)	192-10320
SNP34(E)	32.5	35.1	27.00	34.00	7.5	2.00	POM	Natural (NA)	191-10349
SNP36(E)	34.8	37.1	27.00	34.00	7.5	2.00	POM	Natural (NA)	191-10369
SNP38(E)	36.7	38.9	27.00	34.00	7.5	2.00	POM	Natural (NA)	191-10389
SNP36	37.8	44.0	32.41	43.99	7.3	1.70	PA66GF13	Black (BK)	192-10360
SNP42(E)	41.0	44.2	32.00	45.00	7.5	2.00	POM	Natural (NA)	191-10429
SNP38	41.0	48.1	35.61	57.51	7.3	1.80	PA66GF13	Black (BK)	192-10380
SNP42N	44.5	52.2	35.10	58.93	7.3	1.70	PA66GF13	Black (BK)	191-00005
SNP50(E)	48.8	52.0	32.00	45.00	7.5	2.00	POM	Natural (NA)	191-10509
SNP50	52.2	58.6	36.50	60.40	7.5	1.70	PA66GF13	Black (BK)	192-10500
SNP58(E)	56.7	59.2	31.00	39.00	7.5	2.00	POM	Natural (NA)	191-10589

All dimensions in mm. Subject to technical changes.

Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium-alloy	AL	-40 °C to +180 °C	Natural (NA)		<ul style="list-style-type: none"> Corrosion resistant Antimagnetic 	RoHS
Chloroprene	CR	-20 °C to +80 °C	Black (BK)		<ul style="list-style-type: none"> Weather-resistant High yield strength 	RoHS
Ethylene Tetrafluoroethylene	E/TFE	-80 °C to +170 °C	Blue (BU)	UL94 V0	<ul style="list-style-type: none"> Resistance to radioactivity UV-resistant, not moisture sensitive Good chemical resistance to: acids, bases, oxidizing agents 	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Flexible at low temperature Not moisture sensitive Robust on impacts 	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Bio-plastic, derived from vegetable oil Strong impact resistance at low temperature Very low moisture absorption Weather-resistant Good chemical resistance 	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Good chemical resistance to: acids, bases, oxidizing agents UV-resistant 	HF RoHS
Polyamide 4.6	PA46	-40 °C to +150 °C (5000 h), +195 °C (500 h)	Natural (NA), Grey (GY)	UL94 V2	<ul style="list-style-type: none"> Resistance to high temperatures Very moisture sensitive Low smoke sensitive 	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL94 V2	<ul style="list-style-type: none"> High yield strength 	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL94 V2	<ul style="list-style-type: none"> High yield strength 	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13, PA66GF15	-40 °C to +105 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Good resistance to: lubricants, vehicle fuel, salt water and many solvents 	HF RoHS
Polyamide 6.6, heat and UV stabilised	PA66HSW	-40 °C to +105 °C	Black (BK)	UL94 V2	<ul style="list-style-type: none"> High yield strength Modified elevated max. temperature UV-resistant 	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C	Black (BK), Natural (NA)	UL94 V2	<ul style="list-style-type: none"> High yield strength Modified elevated max. temperature 	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	RoHS
Polyamide 6.6, high impact modified, heat and UV stabilised	PA66HIRHSW	-40 °C to +110 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature Modified elevated max. temperature High yield strength, UV-resistant 	HF RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature Modified elevated max. temperature 	RoHS
Polyamide 6.6, high impact modified, scan black	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Limited brittleness sensitivity Higher flexibility at low temperature 	HF RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL94 V2	<ul style="list-style-type: none"> High yield strength UV-resistant 	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. **More colours on request.

In addition to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers.

*These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

 = Minimum Loop Tensile Strength for Cable Ties (Newton)

HF = Halogenfree
LFH = Limited Fire Hazard
RoHS = Restriction of Hazardous Substances

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6 , with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL94 HB	<ul style="list-style-type: none"> High yield strength Metal and X-Ray detectable 	HF RoHS
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL94 V0	<ul style="list-style-type: none"> High yield strength Low smoke emission 	HF LFH RoHS
Polyamide 6.6 V0 , High Oxygen Index	PA66V0-HOI	-40 °C to +85 °C, (+105 °C, 500 h)	White (WH)	UL94 V0	<ul style="list-style-type: none"> High yield strength Low smoke emissions 	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)	Halogen free	<ul style="list-style-type: none"> UV-resistant Good chemical resistance to: most acids, alkalis and oils 	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL94 V0	<ul style="list-style-type: none"> Resistance to radioactivity Not moisture sensitive Good chemical resistance to: acids, bases, oxidizing agents 	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL94 HB	<ul style="list-style-type: none"> Low moisture absorption Good chemical resistance to: most acids, alcohol and oils 	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL94 V0	<ul style="list-style-type: none"> Low smoke emissions 	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL94 HB	<ul style="list-style-type: none"> Floats in water Moderate yield strength Good chemical resistance to: organic acids 	HF RoHS
Polypropylene, Ethylene- Propylene-Dien- Terpolymere-rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> Good resistance to high temperatures Good chemical and abrasion resistance 	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL94 HB	<ul style="list-style-type: none"> Floats in certain liquids Metal and X-Ray detectable Heat resistant Moderate yield strength Good chemical resistance 	RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL94 V0	<ul style="list-style-type: none"> Low moisture absorption Good chemical resistance to: acids, ethanol and oil 	RoHS
Stainless Steel, Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	Non burning	<ul style="list-style-type: none"> Corrosion resistant Antimagnetic Weather resistant Outstanding chemical resistance 	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL94 HB	<ul style="list-style-type: none"> High elasticity Good chemical resistance to: acids, bases and oxidizing agents 	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In addition to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers.

*These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

**More colours on request.



N = Minimum Loop Tensile Strength
for Cable Ties (Newton)

HF = Halogenfree
LFH = Limited Fire Hazard
RoHS = Restriction of Hazardous Substances