



ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878
Issue date: 22/11/2023 Revision date: 17/05/2023 Supersedes version of: 06/07/2022 Version: 1.1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : ECO Complex Blue FPS
UFI : M7HX-H8WT-Y00P-KYH4
Product code : BDS002638BU
Type of product : Detergent

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Cleaners - Heavy duty

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

CRC Industries Europe B.V.
Touwslagerstraat 1
9240 Zele
Belgium
T +32(0)52/45.60.11 - F +32(0)52/45.00.34
hse@crcind.com - www.crcind.com

1.4. Emergency telephone number

Emergency number : +32(0)52/45.60.11
Office hours: 9-17h CET

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation, Category 2 H319
Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

Causes serious eye irritation.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) : Warning
Hazard statements (CLP) : H319 - Causes serious eye irritation.
Precautionary statements (CLP) : P102 - Keep out of reach of children.
P280 - Wear eye protection/face protection.
P337+P313 - If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

Contains no PBT and/or vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Other information : The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Decan-1-ol, ethoxylated	CAS-No.: 26183-52-8 EC-No.: 500-046-6	< 3	Acute Tox. 4 (Oral), H302 (ATE=500 mg/kg bodyweight) Eye Dam. 1, H318

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. If signs/symptoms develop, get medical attention.

First-aid measures after skin contact : Wash skin with plenty of water. Seek medical attention if irritation develops.

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Seek medical attention if irritation develops.

First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after eye contact : Eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Firefighting instructions : Move containers from fire area if it can be done without personal risk. Use standard firefighting procedures and consider the hazards of other involved materials.

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

- Protective equipment : Wear appropriate protective equipment and clothing during clean-up.
Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes.

6.1.2. For emergency responders

- Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures : Evacuate unnecessary personnel. Ventilate area.

6.2. Environmental precautions

Avoid release to the environment. Avoid the spillage or runoff entering drains, sewers or watercourses.

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : For large spills, confine the spill in a dike and charge it with wet sand or earth for subsequent safe disposal. Following product recovery, flush area with water. Take up small spills with dry chemical absorbent. Clean surface thoroughly to remove residual contamination.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For disposal of contaminated materials refer to section 13 : "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Wear personal protective equipment. Avoid prolonged exposure. Handle in accordance with good industrial hygiene and safety procedures.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store in a well-ventilated place. Keep cool. Keep container closed when not in use.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

Decan-1-ol, ethoxylated (26183-52-8)	
DNEL/DMEL (Workers)	
Long-term - systemic effects, dermal	2080 mg/kg bodyweight/day

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Decan-1-ol, ethoxylated (26183-52-8)	
Long-term - systemic effects, inhalation	294 mg/m³
DNEL/DMEL (General population)	
Long-term - systemic effects, oral	25 mg/kg bodyweight/day
Long-term - systemic effects, inhalation	87 mg/m³
Long-term - systemic effects, dermal	1250 mg/kg bodyweight/day
PNEC (Water)	
PNEC aqua (freshwater)	0.292 mg/l
PNEC aqua (marine water)	0.0292 mg/l
PNEC aqua (intermittent, freshwater)	0.0039 mg/l
PNEC (Sediment)	
PNEC sediment (freshwater)	31.92 mg/kg dwt
PNEC sediment (marine water)	3.19 mg/kg dwt
PNEC (Soil)	
PNEC soil	1 mg/kg dwt
PNEC (STP)	
PNEC sewage treatment plant	1.4 mg/l

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

8.2.2. Personal protection equipment

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Use eye protection according to EN 166. Safety glasses with side shields.

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Wear suitable gloves tested to EN374. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Nitrile gloves are recommended.

8.2.2.3. Respiratory protection

Respiratory protection:

No respiratory protection needed under normal use conditions. In case of insufficient ventilation, wear suitable respiratory equipment. Approved organic vapour respirator. ABEK

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

8.2.2.4. Thermal hazards

Thermal hazard protection:

Not expected to present a significant hazard under anticipated conditions of normal use. Wear appropriate thermal protective clothing, when necessary.

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Blue.
Odour	: characteristic.
Odour threshold	: Not available
Melting point	: Not applicable
Freezing point	: Not available
Boiling point	: Not available
Flammability	: Not applicable
Lower explosion limit	: Not applicable
Upper explosion limit	: Not applicable
Flash point	: Not applicable
Auto-ignition temperature	: > 200 °C
Decomposition temperature	: Not available
pH	: 11
Viscosity, kinematic	: Not available
Solubility	: Soluble in water.
Partition coefficient n-octanol/water (Log Kow)	: Not applicable
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: 1 g/cm ³ at 20 °C
Relative density	: 1 at 20 °C
Relative vapour density at 20°C	: Not available
Particle characteristics	: Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

9.2.2. Other safety characteristics

VOC content : 8 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7). Avoid temperatures exceeding the flash point.

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced. Carbon oxides (CO, CO₂).

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral)	: Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (dermal)	: Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (inhalation)	: Not classified (Based on available data, the classification criteria are not met)

Decan-1-ol, ethoxylated (26183-52-8)

LD50 dermal rabbit	> 3000 mg/kg bodyweight
Skin corrosion/irritation	: Not classified (Based on available data, the classification criteria are not met) pH: 11
Serious eye damage/irritation	: Causes serious eye irritation. pH: 11
Respiratory or skin sensitisation	: Not classified (Based on available data, the classification criteria are not met)
Germ cell mutagenicity	: Not classified (Based on available data, the classification criteria are not met)
Carcinogenicity	: Not classified (Based on available data, the classification criteria are not met)
Reproductive toxicity	: Not classified (Based on available data, the classification criteria are not met)
STOT-single exposure	: Not classified (Based on available data, the classification criteria are not met)
STOT-repeated exposure	: Not classified (Based on available data, the classification criteria are not met)
Aspiration hazard	: Not classified (Based on available data, the classification criteria are not met)

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Adverse health effects caused by endocrine disrupting properties	: The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %
--	--

11.2.2. Other information

No additional information available

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified
Not rapidly degradable	

12.2. Persistence and degradability

ECO Complex Blue FPS

Persistence and degradability	Not established. No data is available on the degradability of this product.
-------------------------------	---

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

12.3. Bioaccumulative potential

ECO Complex Blue FPS

Partition coefficient n-octanol/water (Log Kow)	Not applicable
---	----------------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

ECO Complex Blue FPS

Results of PBT assessment	Contains no PBT and/or vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII
---------------------------	--

12.6. Endocrine disrupting properties

Adverse effects on the environment caused by endocrine disrupting properties : The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %.

12.7. Other adverse effects

Additional information : No other effects known

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
European List of Waste (LoW, EC 2150/2002) : According to the European Waste Catalogue (EWC), Waste Codes are not product specific, but application specific Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
Not regulated for transport				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

VOC Directive (2004/42)

VOC content : 8 g/l

Detergent Regulation (648/2004)

Labelling of contents	
Component	%
non-ionic surfactants, anionic surfactants	<5%
BENZISOTHIAZOLINONE	
METHYLCHLOROISOTHIAZOLINONE, METHYLISOTHIAZOLINONE	

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified

ECO Complex Blue FPS

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Abbreviations and acronyms:

vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H302	Harmful if swallowed.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC. The products are governed by Regulation (EC) No 1272/2008 on the classification, labelling and packaging of substances and mixtures (CLP); Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (in each case, as amended and replaced) and other applicable laws. It is an importers or downstream users responsibility to ensure compliance of product they import. An SDS provided in the official language(s) of a country is not a guarantee of compliance in that country.