



Technical Data

| | |
|-------------------|-------------------------|
| number of pins | 8 |
| power | 4 (3+PE) |
| signal | 4 |
| temperature range | -20 °C to 130 °C |
| clamping range | Ø 9.5 mm to Ø 14.5 mm |
| protection type | when connected IP 66/67 |

Electrical Data

| | power | signal |
|--------------------------------|--------------|---------------|
| rated current | max. 30 A* | max. 7 A* |
| rated voltage | 630V (AC/DC) | 250 V (AC/DC) |
| rated insulation voltage (L-L) | 6000 V | 2500 V |

| | |
|---------------|-----|
| mating cycles | 500 |
|---------------|-----|

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

| | |
|---------------------------|--------|
| pollution degree | 3 |
| over voltage category | III |
| max. height for operation | 2000 m |

Material

| | |
|-------------------|------------------------------|
| housing | zinc diecast / nickel plated |
| insulation insert | PA 6.6 mod., UL 94/V0 |
| seals | FKM |
| clamp ring | brass / nickel plated |

Contacts (not part of product contents)

Tools (not part of product contents)

B KU A 199 NN 00 42 0100 000



Contact Arrangement
mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Deutschland
Tel.: +49 9962 2002-0
Fax: +49 9962 2002-70
E-Mail: intercontec@te.com
Web: www.intercontec.biz



Main Dimensions
Extension

*for max. wire cross-section
pay attention to the
cross-section of used contacts