

Supplier	Article description			Art. No. / EAN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden pump GP 5000 INOX			31372	24 Months
	Master Box Information				
	Master Box dimensions in cm			weight (kg) gross	pack. Unit (pcs.)
	Width	Depth	Height		
-	-	-	-	-	
Article Information					
Color Box dimensions in cm			weight (kg) net / gross	Qty.	
Width	Depth	Height			
40.0	22.5	29.5	9 / 10,4	1	

Garden pump GP 5000 INOX	quantity / pallet:	
	quantity / truck:	

Description:

Robust, self-priming jet pump with garden steel pump housing, on-off switch and ergonomic handle. For pumping clear water. For filling and emptying water tanks, etc. Due to the high efficiency, this device is also well suited for the operation of sprinklers.

Technical Data:

Nominal performance: 1,200 Watt
 Delivery height max.: 45 m / 4.5 bar
 Flow rate max.: 83 l/min / 5,000 l/h
 Suction height max.: 9 m
 Pump housing: stainless steel
 Pressure port: 30.93 mm (1" female)
 Suction port: 30.93 mm (1" female)
 Temp. max. liquid: 35 °C
 Power cord: 1.5 m / H07RN-F
 Number of sprinklers max.: 5



Approval marks:

