

Product Information

without engagement until placement of order

Supplier	Article description	Art. No. / EAN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden pump with 4 m suction Kit Clean Jet 1300 Plus	30087	24 Months	
		4011458300877		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	
-	-	-	-	
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	
Width	Depth	Height		
38,5	31,5	34,0	9,7 / 12,3	

Garden pump with 4 m suction Kit
Clean Jet 1300 Plus

quantity / pallet:

quantity / truck:

Description:

This garden pump is equipped with a robust pump housing made of high-grade steel. Clean Jet 1300 Plus is a self-priming pump for watering the garden or emptying ponds or basins.

A 4 metre suction hose is already included.

Maintenance-free capacitor motor with thermal overload protection.

Pump housing high grade steel

Hydraulic unit: Noryl

Application-friendly, ergonomically shaped handle.

Pre-assembled on a solid steel base plate.

Technical Data:

Nominal performance:	1200 Watt
Delivery height max / pressure.:	50 m / 5 bar
Flow rate max.:	73 l/min / 4,400 l/h
Suction height max.:	9 m
Pump housing:	stainless steel
Suction port:	30,93 mm (1"), female
Pressure port:	30,93 mm (1"), female
Fluid temp. max.:	35 °C
Power cord:	1,5 m / H07RN-F
Number of sprinklers max.:	5
Suction kit:	4m



Approval marks:

