

Supplier	Article description			Art. No. / EAN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Booster set HW 1300/25 Plus TLS			31158	24 Months
	Master Box Information				
	Master Box dimensions in cm			weight (kg) gross	pack. Unit (pcs.)
	Width	Depth	Height		
Article Information					
Color Box dimensions in cm			weight (kg) net / gross	Qty.	
Width	Depth	Height			
51,0	29,0	61,0	14,41 / 16,40	1	

Booster set HW 1300/25 Plus TLS	quantity / pallet:	18
	quantity / truck:	594

Description:

HW 1300/25 Plus TLS is powerfull, high efficient allround model with high-grade steel pump housing. It has a very wide application area:

Automatic domestic water supply from wells and cisterns, garden watering and automated irrigation, ideally suited for pressure boosting. The integrated dry-running protection prevents damage to the hydraulic unit from interference by water shortage.

Technical implementation:

Unattended condenser motor including thermo-overload protection, pressure tank including EPDM food-proof membrane, pump impeller made of Noryl PRO.

Technical Data:

Nominal performance:	1,200 Watt
Delivery height / Pressure	50 m / 5 bar
Flow rate max.:	73 l/min / 4,350 l/h
Self-priming hight max.:	9 m
Pump housing:	Stainless steel
Pressure tank / Volume:	Steel / 22 l
Pressure port:	30.93 mm (1", female)
Suction port:	30.93 mm (1", female)
Fluid temp. Max.:	35 °C
Power cord:	1.5 m / H07RN-F
Sprinklers max.:	4 pcs.



Approval marks:

