

Product Information

without engagement until placement of order

Supplier	Article description			Art. No. / GTIN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Booster Set HWW K-1000/50 Plus			30189	24 Months
				4011458301898	
	Master Box Information				
	Master Box dimensions in cm			weight (kg) gross	pack. Unit (pcs.)
	Width	Depth	Height		
-	-	-	-	-	
Article Information					
Color Box dimensions in cm			weight (kg) net / gross	Qty.	
Width	Depth	Height			
59,0	43,2	66,5	15,2 / 17,9	1	

Booster Set
HWW K-1000/50 Plus

quantity / pallet:

quantity / truck:

Description:

Due to its robustness and impressive performance data, the HWW K-1000/50 Plus is the perfect device for many applications. The plastic pump housing makes the HWW K-1000/50 Plus work very silent. It is equipped with a high quality EPDM-membrane and a pressure gauge. Coming along with a big 50 l tank, it works very energy efficient. A maintenance-free capacitor motor with a thermal overload protection is included. The pump housing is made of shock resistant plastic and the hydraulic unit is made of noryl. The area of applications are: automatic domestic water supply from wells and cisterns, garden and automatic irrigation.

Technical Data:

Nominal performance: 800 Watt
 Delivery height / pressure max.: 46 m / 4.6 bar
 Flow rate max.: 58 l/min / 3,500 l/h
 Suction height max.: 9 m
 Pump housing: Plastic
 Pressure tank / Volume: Steel / 50 l
 Pressure port: 33,25 mm (1", male)
 Suction port: 33,25 mm (1", male)
 Fluid temp. max.: 35 °C
 Power cord: 1.5 m / H05RN-F
 Number of sprinklers max.: 3



Approval marks:

