



Discover more details and matching accessories online!

## High-resolution crane scale for loads up to 300 kg

### Features

- **1** With the TÜV certification mark, the scales meet the requirements of the standard EN 13155 (Non-fixed load lifting attachments/ Breakage resistance) and EN 61010-1 (Electrical safety)
- Fully-equipped crane scale for low to medium load ranges. The solid design guarantees that extra level of safety (TÜV tested). Thanks to the large LCD display and the remote control which is delivered as standard, it can also be operated safely from a distance and results can be read off
- Thanks to battery operation/rechargeable battery operation (optional), compact, light-weight construction, it is suitable for the use in several locations
- Battery level indicator, LED visual display
- Hold function: For easy reading of the weighing result, the display can be „frozen“ in different ways. Either automatically when the weighing value remains unchanged or manually by pressing the Hold key

- Tare: Resets the display to „0“ when there is a load on the scale. Now removed or added loads are directly displayed
- Large high-contrasted display that is easy to read
- Standby function: display automatically switched off after 5 min without a change of load. Automatic activation with the touch of a key
- Hook with safety catch, revolving
- Shackle and safety catch made of nickel-plated steel
- **2** Infrared remote control standard, range up to 20 m, W×D×H 65×24×100 mm, batteries included

### Technical data

- Backlit LCD display, digit height 28 mm
- Ready for use: Batteries included, 4×1.5 V AA, operating time up to 100 h
- Precision: 0,2% of [Max]
- Weighing units: kg, lb, N
- Permissible ambient temperature 5 °C/40 °C

#### STANDARD



#### OPTION



| Model                                                                                                                                                       | Weighing capacity<br>[Max]<br>kg | Readability<br>[d]<br>g | Net weight<br>approx.<br>kg | 3 Dimensions |         |         |         |         |         |         | Options             |                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|-------------------------|-----------------------------|--------------|---------|---------|---------|---------|---------|---------|---------------------|---------------------|
|                                                                                                                                                             |                                  |                         |                             | A<br>mm      | B<br>mm | C<br>mm | D<br>mm | E<br>mm | F<br>mm | G<br>mm | Calibr. Certificate | DAkKS accr.<br>KERN |
| <b>KERN</b>                                                                                                                                                 |                                  |                         |                             |              |         |         |         |         |         |         |                     |                     |
| <b>HCD 60K-2*</b>                                                                                                                                           | 60                               | 20                      | 1,2                         | 150          | 79,3    | 97,7    | 276,1   | 246,5   | 26      | 18      | 963-129H            |                     |
| <b>HCD 100K-2</b>                                                                                                                                           | 150                              | 50                      | 1,2                         | 150          | 79,3    | 97,7    | 276,1   | 246,5   | 26      | 18      | 963-129H            |                     |
| <b>HCD 300K-1</b>                                                                                                                                           | 300                              | 100                     | 1,2                         | 150          | 79,3    | 97,7    | 276,1   | 246,5   | 26      | 18      | 963-129H            |                     |
| Multi-division balance, with increasing or decreasing load, it switches automatically to the next largest or smallest weighing range [Max] and readout [d]. |                                  |                         |                             |              |         |         |         |         |         |         |                     |                     |
| <b>HCD 100K-2D</b>                                                                                                                                          | 60   150                         | 20   50                 | 1,2                         | 150          | 79,3    | 97,7    | 276,1   | 246,5   | 26      | 18      | 963-129H            |                     |
| <b>HCD 300K-2D</b>                                                                                                                                          | 150   300                        | 50   100                | 1,2                         | 150          | 79,3    | 97,7    | 276,1   | 246,5   | 26      | 18      | 963-129H            |                     |

**1** \* ONLY WHILE STOCKS LAST