Safety control unit



Model Number


SB4-OR-4XP-4M


Safety control unit Safety control unit of series SB4

Features

- ٠ Evaluation unit for security throughbeam sensors SLA5(S) and SLA40; for safety light grids SLP, for safety light curtains SLC; for switching pads and emergency stop buttons of categories 2 and 4
- 4 sensor channels ٠
- Self-monitoring (type 4 according to . IEC/EN 61496-1)
- Operating mode can be selected by • means of DIP switches
- Start/Restart disable
- Relay monitor ٠
- Sequential and parallel muting in va-• rious operating modes
- ٠ Double muting
- Emergency muting for the correction • of the material jam
- Pre-fault indication •
- Clearly visible LED functional display •
- 7-segment diagnostic display •
- Safety outputs OSSD, external status • displays OSSD

Dimensions





Electrical connection

11☆12☆11☆

₩ B4

. ₩ R3 ₩R2

🛱 R1

1 2 3 4 2

6000 6000 60

0000000000000

Slot 2 Slo

314 15 16 10 11 12 13141: 9101

₩ OSSE . ∦⊂RI

8.

Slot 1

2 3 4

Terminal	Function
1	Reset input; normally closed contact
2	Restart input (RI); normally closed contact
3	24 V DC connection for reset, restart and RM
4	Relay monitor (RM)
5 - 6	OSSD1; potential free relay contact;
	normally open contact
7 - 8	OSSD2; potential free relay contact;
	normally open contact
9	Signal output OSSD OFF
10	Signal output OSSD ON
11	Signal output restart
12	Leave free (n.c.)
13	+24 V DC supply voltage
14	0 V DC supply voltage
15	Earth
16	Leave free (n.c.)

al Function 24 V sensor sup Sensor 2 IN Sensor 4 IN Sensor 4 IN 0 V sensor supply 24 V sensor supply Sensor 1 IN Sensor 3 IN 0 V sensor supply Input override 24 V override 1 24 V override Input or erride 2 +24 V DC supply voltage for muting lamps 0 V DC supply voltage for muting lamps ng lamp Output muting lamp 2

Start/restart disable, relay monitor, muting operating modes

Terminal	Function	Channel	Connection	Connection 2-channel	Connection
		classification	Beam sensor / Light grid safety feature	p ON	Switching pad
1	Receiver 2 Input	Input	Receiver output 2	OSSD Output 1.2	Switching pad 1.4
2	Sensor 2 24 V DC +U	Channel 2	24 V Receiver2	24 V Power supply 1	
3	Sensor 2 Mass GND]	0 V Receiver 2, Emitter 2	0 V Power supply 1	
4	Emitter 2 Output	Output	Emitter input 2		Switching pad 1.3
5	Receiver 1 Input	Input	Receiver output 1	OSSD Output 1.1	Switching pad 1.2
6	Sensor 1 24 V DC +U	Channel 1	24 V Receiver 1		
7	Sensor 1 Mass GND	1	0 V Receiver 1, Emitter 1		
8	Emitter 1 Output	Output	Emitter input 1		Switching pad 1.1
9	Emitter 3 Output	Output	Emitter input 3		Switching pad 2.4
10	Sensor 3 Mass GND	Channel 3	0 V Receiver 3, Emitter 3	0 V Power supply 2	
11	Sensor 3 24 V DC +U]	24 V Receiver 3	24 V Power supply 2	
12	Receiver 3 Input	Input	Receiver output 3	OSSD Output 2.2	Switching pad 2.3
13	Emitter 4 Output	Output	Emitter input 2		Switching pad 2.2
14	Sensor 4 Mass GND	Channel 4	0 V Receiver 4, Emitter 4	0 V Receiver 4, Emitter 4	
15	Sensor 4 24 V DC +U	1	24 V Receiver 4		
16	Receiver 4 Input	Input	Receiver output 4	OSSD Output 2.1	Switching pad 2.1

Technical data

General specifications

Operating mode

Functional safety related parameters				
Safety Integrity Level (SIL)		SIL 3		
Performance level (PL)		PL e		
Category		Cat. 4		
Mission Time (T _M)		20 a		
PFH _d		3.5 E-9		
B _{10d}		see instruction manuals		
Туре		4		
Indicators/operating means				
Diagnostics indicator		7-segment display		
Function indicator		LED red: OSSD OFF LED green: OSSD ON Yellow LED: start readiness channel 1 - 4 LED yellow: switching state (receiver)		
Pre-fault indicator		LED yellow flashing: Indicator lamp channel 1 4		
Electrical specifications				
Operating voltage	UB	24 V DC, ± 20 %		
No-load supply current	I ₀	500 mA		
Input				

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001 www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



1

Safety control unit

Activation current	approx. 7 mA			
Activation time	0.4 1.2 s			
Test input	Reset-input for system test			
Output				
Safety output	2 relay outputs, force-guided NO-contact			
Signal output	1 PNP each, max. 300 mA for start readiness, OSSD on, OSSD off, muting lamp			
Switching voltage	10 V 250 V AC/DC			
Switching current	min. 10 mA , max. 6 A AC/DC			
Switching power	DC: max. 24 VA AC: max. 230 VA			
Response time	38 ms			
Conformity				
Functional safety	ISO 13849-1 ; EN 61508 part1-4			
Product standard	EN 61496-1			
Ambient conditions				
Ambient temperature	0 50 °C (32 122 °F)			
Storage temperature	-20 70 °C (-4 158 °F)			
Mechanical specifications				
Degree of protection	IP20			
Connection	screw terminals , lead cross section 0.2 2 mm ²			
Material				
Housing	Polyamide (PA)			
Mass	430 g			
Approvals and certificates				
CE conformity	CE			
UL approval	cULus			
TÜV approval	TÜV			
Function				

The evaluation system SB4 is an ESPE of type 4 (EN 61496-1 or IEC 61496-1) or category 4 (EN 954-1). This system is also designed and tested according to IEC 61508. It meets the requirements for the SIL3.

The operating instructions supplied with the device must be observed for planning, installation and operation.

A maximum of 4 safety light barriers can be connected to the evaluation device.

With the sensor card on position 2, it is possible to connect "3-wire" light barriers of the SLA family (for example SLA5) and light grids of the SLP type. But also p-switching safety devices with dedicated cross circuit monitoring can be connected, for example safety light curtains from the SLC family. In addition switch-off mats of the 4-wire principle or integrated safety sensors in the 1 or 2 channel version can be connected.

The cable or the manner it is laid to the light barriers and light grids must be chosen that no short circuit between the receiver and transmitter wires is possible.

Light curtains with semiconductor switch outputs and integrated safety sensors in 2 channel design are monitored for simultaneousness. The monitoring time is 2 s.

The connection is done on channels 3 and 4 and/or 1 and 2. Note that these sensors must feature a dedicated cross circuit monitoring, because the module does not

carry out the cross circuit monitoring for these sensors. Integrated safety sensors, which are connected to the Safebox must work according to the normally closed principle.

An open contact means "safe status". Switch-off mats of the 4-wire principle can be connected to channels 1 and 2 and/or 3 and 4.

The module on position 3 implements the muting function. Refer to the operating instructions for detailed notes on the functions.

The user must make sure to only connect sensors that can be muted to the sensor card that is assigned to the muting module. These are, for example, light barriers or light grids.

Operating modes

By default, the restart interlock is activated.

Each assembly contains DIP switches for selecting the functions. For selecting functions, 2 selector switches must always be actuated.

fa-info@sg.pepperl-fuchs.com

fa-info@de.pepperl-fuchs.com

Switches on the first assembly:

w.pepperl-fuchs.com

	Switch	Position	Operating mode		
R	efer to "General Notes Rela	ting to Pepperl+Fuchs Prod	uct Information".		
Pe	epperl+Fuchs Group	USA: +1 330 486 00	001 Germany: +49 621 776 4411	Singapore: +65 6779 9091	

fa-info@us.pepperl-fuchs.com



Safety control unit

1 and 3	OFF	Without restart interlock (restart, RI)	
	ON	With restart interlock (restart, RI)	
2 and 4	OFF Without relay monitor (RM)		
	ON	With relay monitor (RM)	

Switches on the second assembly:

The assembly contains 6 DIP switches for selecting the sensor type and the position. Six possibilities are offered for combining sensors. The desired combination is to be set binary. For function selection, always 2 switches must be actuated, that means DIP switches 1 - 3 have the same switch position as DIP switches 4 - 6.

DIP switch		ı	Operating mode	
3 and 6	2 and 5	1 and 4		
0	0	0	SLA /SLP/bridge channel 1 + 2 and channel 3 + 4	
0	0	1	SLA /SLP/bridge on channel 1 + 2 and SLC channel 3 + 4	
0	1	0	SLC channel 1 + 2 and channel 3 + 4	
0	1	1	SLA /SLP/bridge channel 1 + 2 and safety mat channel 3 + 4	
1	0	0	Safety mat channel 1 + 2 and channel 3 + 4	
1	0	1	SLC channel 1 + 2 and safety mat channel 3 + 4	

Switches on the third assembly:

Switch	Position	Operating mode
1	OFF	Muting lamp monitoring inactive
Group 1 and 2	ON	Muting lamp monitoring active
2	OFF	Single muting
Group 1 and 2	ON	Double muting
3	OFF	Time window-limited muting
Group 1 and 2	ON	Protection beam-limited muting
4	OFF	Sequential muting
Group 1 and 2	ON	Parallel muting

Displays

The OSSD-R/supply module on position 1 has a red/green LED for indicating the OSSD on/off statuses, a yellow LED for the start-ready status and a 7 segment display for system diagnosis.

The 7 segment display indicates the status and the error codes of the system.

Display	7 segment display		
1	DIP switch positions differ		
2	Incorrect configuration		
3	Time-out at one or more muting sensors		
4	Transmitter error		
6	Muting lamp error		
7	Simultaneousness monitoring error		
8	Receiver error		
9	Error at sensor channel		
С	Error at sensor channel		
E	System error		
F	Relay monitor error		
Н	Selection chain error		
L	Configuration error		
U	Low voltage or voltage surge detected		

Release date: 2017-12-06 14:47 Date of issue: 2017-12-06 192147_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

