



Mounting dimensions for swivel

Electrical connection







Mounting dimensions with mounting bracket set AIR30

132.5 144.

16

Model Number

CE

AIR30-8-H-2500/38a


Active infrared scanner with 5 m fixed cable

Features


- Single-beam light scanner •
- Can be used to monitor both main and ٠ ancillary closing edges
- Closing edge safety on revolving ٠ doors and carousel doors
- Accurate beam alignment thanks to fi-• nely bundled light beam
- Background suppression operating ٠ mode: ignores objects outside the sensing range

Product information

AIR30 is a series of active infrared scanners with excellent optical properties for monitoring closing edges in a wide range of door systems. The diverse range of housings and mounting options allow the devices to be adapted to suit a whole host of mounting conditions.



Indicators/operating means



1	Transmitter
2	Indication-LED
3	Detection range adjuster
4	Light / Dark switch
5	Receiver

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical data

General specifications 550 ... 1000 mm Detection range min. Detection range max. 550 ... 2500 mm IRED Light source modulated infrared light Light type Black/White difference (6 %/90 %) ≤ 400 mm at a distance of 2000 mm Transmitter frequency 1800 Hz Operating mode Background suppression 50 mm at 2000 mm sensor range Diameter of the light spot Angle of divergence approx. 1.4 Swivel bracket, Mounting bracket Accessories provided Functional safety related parameters 1050 a MTTF_d Mission Time (T_M) 20 a Diagnostic Coverage (DC) 90 % Indicators/operating means Function indicator LED red: lights up when output is active Control elements Sensing range adjuster, light-on/dark-on changeover switch **Electrical specifications** 10 ... 48 V DC / 11 ... 36 V AC Operating voltage U_B No-load supply current 100 mA I0 Input Test input emitter deactivation at +UB Output Switching type light/dark on, switchable Signal output relay, 1 NO Switching voltage ≤ 50 V AC / 24 V DC Switching current ≤ 200 mA AC / 1 A DC 70 ms Response time De-energized delay approx. 200 ms Ambient conditions -20 ... 60 °C (-4 ... 140 °F) Ambient temperature -20 ... 75 °C (-4 ... 167 °F) Storage temperature **Mechanical specifications** IP52 Degree of protection Connection 5 m fixed cable Material Housina plastic Optical face Luran® Mass 50 g Compliance with standards and directives Directive conformity EMC Directive 2004/108/EC EN 60947-5-2:2007+A1:2012 Standard conformity Product standard EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012 Standards EN 61000-6-2:2005 + AC:2005 excluding EN 61000-4-5, EN 61000-4-11 EN 61000-6-3:2007+A1:2011

Approvals and certificates

CCC approval

Certified by China Compulsory Certification (CCC)

Typical applications

- · Monitoring closing edges and crushing points on revolving doors and carousel doors
- Door monitoring system in local public transportation

Detection area



Accessories

UP-Einbaurahmen Mounting frame for sensors in the AIR30 and PROSCAN series

Flush Mounting AIR30

Installation cover for AIR30 series sensors

Wetterhaube AIR30

Weather hood for series AIR30

Other suitable accessories can be found at www.pepperl-fuchs.com


2


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Curves/Diagrams







Operating principle

Active infrared scanners detect people and objects using short-wave infrared radiation according to the triangulation principle. A switch signal is tripped if the infrared beam emitted is reflected by an object within the specified sensing range. Where background suppression is activated, the background (e.g. ground) is detected but not evaluated.

This allows an extremely precise detection area to be set and ensures reliable detection of people, vehicles and other objects.

Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Function principle background suppression

Object in scanning field:





4