



Data Sheet

20pcs 2:1 Thin Wall Heat Shrinking Tube Set Typ. T1904CA042



Material: Polyolefin
 Shrinking ratio: 2:1
 Tensile strength: $\geq 10.3\text{Mpa}$
 Withstand voltage: 2kv/60s
 Volume resistance: $\geq 10^{14}\ \Omega/\text{cm}$
 Flammability: VW-1
 Operating Temperature: $-55 \sim 110^\circ\text{C}$
 Minimum shrink temperature: 70°C
 Full recovery temperature: 110°C



Nominal size (mm)	Before shrink(ømm)		After shrink(ømm)		Length	Contents
	Inner dia.	W.T	I.D. (max.)	W.T (min.)		
ø2.0	2.5±0.3	0.20±0.05	1.00	0.44	500 mm	4 pc
ø2.5	3.0±0.3	0.25±0.05	1.25	0.44	500 mm	4 pc
ø3.5	4.0±0.3	0.25±0.05	1.75	0.44	500 mm	4 pc
ø4.5	5.0±0.3	0.25±0.05	2.25	0.44	500 mm	4 pc
ø6.0	6.5±0.3	0.28±0.05	3.00	0.56	500 mm	4 pc