



Item no.: 2108776 / 2108780 / 2108768 / 2108789 / 2108781 /
2108756 / 2108766 / 2108782 / 2108760

Data Sheet

2:1 Thin Wall Heat Shrinking Tube Set



Material: Polyolefin
 Shrinking ratio: 2:1
 Tensile strength: $\geq 10.3\text{Mpa}$
 Withstand voltage: 2kv/60s
 Volume resistance: $\geq 10^{14}\Omega/\text{cm}$
 Flammability: VW-1
 Operating Temperature: $-55 \sim 110^\circ\text{C}$
 Minimum shrink temperature: 70°C
 Full recovery temperature: 110°C



Type	Nominal size (mm)	Before shrink(ømm)		After shrink(ømm)		Contents
		Inner dia.	W.T	I.D. (max.)	W.T (min.)	
T1904CA026	ø1.5	2.0±0.3	0.20±0.05	0.80	0.36	1 meter
T1904CA027	ø2.0	2.5±0.3	0.20±0.05	1.00	0.44	1 meter
T1904CA028	ø2.5	3.0±0.3	0.25±0.05	1.25	0.44	1 meter
T1904CA029	ø3.5	4.0±0.3	0.25±0.05	1.75	0.44	1 meter
T1904CA030	ø4.5	5.0±0.3	0.25±0.05	2.25	0.44	1 meter
T1904CA031	ø6.0	6.5±0.3	0.28±0.05	3.00	0.56	1 meter
T1904CA032	ø9.0	9.6±0.3	0.30±0.07	4.50	0.56	1 meter
T1904CA033	ø12.0	13±0.4	0.30±0.07	6.00	0.56	1 meter
T1904CA034	ø25.0	26±1.0	0.45±0.10	12.5	0.87	1 meter