

 ϵ







Model Number


LA31/LK31/16/25/31/115

Thru-beam sensor with 2 m fixed cable


Features

- Cost-optimized series for standard
- Large construction with small housing
- Highly visible LED
- Version for universal voltages
- Relay output
- Wide range of mounting options

Dimensions



Electrical connection



		_

Technical data				
System components				
Emitter		LA31/115		
Receiver		LK31/16/25/31/115		
General specifications				
Effective detection range		0 30 m		
Threshold detection range		43 m		
Light source		LED		
Light type		modulated visible red light , 630 nm		
Alignment aid		LED yellow: 1. LED illuminates: Sufficient light signal received, emitter and receiver alignment is correct 2. LED flashes: Reaching switching point 3. LED off: Light beam is interrupted or the alignment is out		
Diameter of the light spot		approx. 800 mm at a distance of 30 m		
Angle of divergence		Emitter: 0.5 °, Receiver: 1.5 °		
Ambient light limit		50000 Lux ; according EN 60947-5-2		
Functional safety related para	meters			
MTTF _d		620 a		
Mission Time (T _M)		20 a		
Diagnostic Coverage (DC)		0 %		
Indicators/operating means				
Operation indicator		LED green: power on		
Function indicator		LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point		
Control elements		sensitivity adjustment		
Electrical specifications		constantly adjacement		
Operating voltage	U_B	24 240 V AC 12 240 V DC		
No-load supply current I ₀		Emitter: ≤ 20 mA Receiver: ≤ 20 mA		
Power consumption P ₀		Emitter: ≤ 1 VA Receiver: ≤ 1 VA		
O. 1		neceiver. ≤ 1 vA		
Output				
Switching type		light on		
Signal output		Relay, 1 alternator		
Switching ourrent		max. 250 V AC/DC		
Switching current		max. 3 A		
Switching power		DC: max. 150 W AC: max. 750 VA		
Switching frequency	f	≤ 20 Hz		
Response time		≤ 25 ms		
Ambient conditions				
Ambient temperature		-25 55 °C (-13 131 °F)		
Storage temperature		-40 70 °C (-40 158 °F)		
Mechanical specifications				
Degree of protection		IP67		
Connection		Emitter: 2 m fixed cable , 2-wire Receiver: 2 m fixed cable , 5-wire		
Material				
Housing		Polycarbonate		
Optical face		PMMA		
Mass		Emitter: 116 g Receiver: 131 g		
Compliance with standards at ves	nd directi	•		
Directive conformity		EMC Directive 2004/108/EC		
Standard conformity				
Product standard		EN 60947-5-2:2007		
Standards		IEC 60947-5-2:2007 EN 62103		
A				
Approvals and certificates EAC conformity		TR CU 020/2011		
Protection class		TR CU 004/2011 II , rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN E0178, rated insulation voltage 240 V AC		
CCC approval		cuit according to EN 50178, rated insulation voltage 240 V AC Certified by China Compulsory Certification (CCC)		

Accessories

OMH-RL31-01

Mounting bracket

OMH-RL31-02

Mounting bracket narrow

OMH-RL31-03

Mounting bracket narrow

OMH-RL31-04

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

OMH-RL31-05

Mounting bracket with M10 threaded rod

OMH-RL31-06

Stainless steel mounting bracket with adjustable half clamp on the side

Other suitable accessories can be found at www.pepperl-fuchs.com

Curves/Diagrams

