























Features

- Charger for lead-acid batteries (Gel, flooded and AGM) and Li-ion batteries (lithium iron and lithium manganese)
- Built-in default 3 stage charging curves and programmable curve
- Built-in I²C interface, PMBus protocol (Optional CANBus protocol)
- · Output voltage and current programmable
- Universal AC input / Full range
- · Built-in active PFC function
- · Forced air cooling by built-in thermal controlled DC fans
- Built-in OR-ing FET, support hot swap (hot plug)
- · Active current sharing up to 12800W for one 19" rack shelf
- Protections: Battery under voltage / Battery no connection
 / Short circuit / Over voltage / Over temperature
- · Optional conformal coating
- 5 years warranty

Applications

- Large scale DC UPS or emergency backup system
- Marine battery charger module
- Electric scooter or vehicle charger station
- · Wastewater treatment system
- Electrolysis system


■ GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

Description

DBR-3200 is a 3200W single output AC/DC front-end charger in 1U low profile with high power density, 37W/inch³. It is an intelligent charger that has pre-loaded programmable charging curves for different types of lead-acid and li-ion batteries. Output programmable function allows user to adjust the charging voltage and current via the built-in potentiometer or PMBus protocol. Various protection mechanisms as well as the temperature compensation function are provided to assure normal and safe system operation. The rack-mountable attribute fits DBR-3200 perfectly for the charging, backup or constant current source applications exploiting the rack architecture or central power management.

■ Model Encoding / Order Information



Note: 19" rack shelf, DHP-1UT, available.

Туре	Communication Protocol	Note
Blank	PMBus protocol	In Stock
CAN	CANBus protocol	By request

3200W Rack Mountable Front End Battery Charger


SPECIFICATION

MODEL		DBR-3200-24	[DBR-3200-48		
	BOOST CHARGE VOLTAGE(Vboost)(default)	28.8V	57.6V			
	FLOAT CHARGE VOLTAGE(Vfloat)(default)	27.6V	5	55.2V		
	CONSTANT CURRENT(CC)(default)					
		By built-in potentiometer, SVR				
OUTPUT	VOLTAGE ADJ. RANGE	23.5 ~ 30V	4	7.5 ~ 58.8V		
	RECOMMENDED BATTERY					
	CAPACITY(AMP HOURS) Note.3	330 ~ 1000Ah	1	80 ~ 550Ah		
	LEAKAGE CURRENT FROM					
	BATTERY (Typ.)	<1.5mA				
		90 ~ 264VAC 127 ~ 370VDC				
	FREQUENCY RANGE	47 ~ 63Hz				
	POWER FACTOR (Typ.)	0.97/230VAC at full load				
INPUT	EFFICIENCY (Typ.)	93.5% 94.5%				
INFUI	AC CURRENT (Typ.) Note.4					
	INRUSH CURRENT (Typ.)	COLD START 55A/230VAC				
	LEAKAGE CURRENT	<1.5mA / 230VAC				
	LLANAGE CONNENT			72 751/		
	OVER VOLTAGE	31.5 ~ 37.5V		63 ~ 75V		
PROTECTION	OVER TEMPERATURE	Protection type : Shut down o/p volta	<u> </u>	an dayun		
	OVER TEMPERATURE	Shut down o/p voltage, recovers auto	, ,			
				al output voltage. Please refer to the Function Manual.		
	OUTPUT CURRENT PROGRAMMABLE(PC)	, ,		current. Please refer to the Function Manual.		
	AUXILIARY POWER	5V @ 0.3A, tolerance ±10%, ripple	117 0 7	7 11 11		
FUNCTION	REMOTE ON-OFF CONTROL	By electrical signal or dry contact Power ON:short Power OFF:open. Please refer to the Function Manual				
	TEMPERATURE COMPENSATION					
	DC OK SIGNAL	The isolated TTL signal out. Please refer to the Installation Manual				
	AC OK SIGNAL	The isolated TTL signal out. Please r				
	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curv	/e")			
	WORKING HUMIDITY	20 ~ 90% RH non-condensing				
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing				
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)				
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes				
	SAFETY STANDARDS	UL62368-1, CSA C22.2 No. 62368-1, TUV BS EN/EN62368-1, EAC TP TC 004 approved				
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2KVAC (
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms				
		Parameter	Standard	Test Level / Note		
		Conducted	BS EN/EN55032 (CISF	,		
	EMC EMISSION	Radiated	BS EN/EN55032 (CISF	PR32) Class A		
		Harmonic Current	BS EN/EN61000-3-2			
SAFETY &		Voltage Flicker	BS EN/EN61000-3-3			
EMC		BS EN/EN55024, BS EN/EN61000-6				
(Note 5)		Parameter	Standard	Test Level / Note		
		ESD	BS EN/EN61000-4-2	Level 3, 8KV air ; Level 2, 4KV contact		
		Radiated	BS EN/EN61000-4-3	Level 3		
	EMC IMMUNITY	EFT / Burst	BS EN/EN61000-4-4	Level 3		
		Surge	BS EN/EN61000-6-2	2KV/Line-Line 4KV/Line-Earth		
		Conducted	BS EN/EN61000-4-6	Level 3		
		Magnetic Field	BS EN/EN61000-4-8	Level 4		
		Voltage Dips and Interruptions	BS EN/EN61000-4-11	>95% dip 0.5 periods, 30% dip 25 peri >95% interruptions 250 periods		
	MTBF	528.8K hrs min. Telcordia SR-332	(Bellcore); 44.4K hrs min.	MIL-HDBK-217F (25°C)		
OTHERS	DIMENSION	325*107*41mm (L*W*H)				
	PACKING	2.65Kg;4pcs/11.6Kg/0.93CUFT				
NOTE	All parameters NOT special This is MEAN WELL's sugg Derating may be needed ur The charger is considered a 600mm*900mm metal play perform these EMC tests, p The ambient temperature delayers.	er specification may be required for different battery specification. Please contact battery vendor and MEAN WELL for details. pecially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. It is suggested range. Please consult your battery manufacturer for their suggestions about maximum charging current limitation. It is ded under low input voltages. Please check the derating curve for more details. It is ered a component which will be installed into a final equipment. All the EMC tests are been executed by mounting the unit on tall plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to lests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) ture derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft). aimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx				
				File Name:DBR-3200-SPEC 2022-		




■ BLOCK DIAGRAM


PFC fosc: 110KHz PWM fosc: 90KHz



■ DERATING CURVE

■ STATIC CHARACTERISTICS







■ FUNCTION MANUAL


1.PMBus Communication Interface

X DBR-3200 supports PMBus Rev. 1.1 with maximum 100KHz bus speed, allowing information reading, status monitoring, output trimming, etc. For details, please refer to the Installation Manual.

2. Charging Curve

- * By factory default, this charger performs the default curve which can be programmed via PMBus.
- X To disable / enable the charging curve, change to a 2 stage curve, a different curve frequently used for certain types of batteries in the industry, and so on, please refer to the Installation Manual.
- X To program the parameters of the charging curve, SBP-001, the smart battery charging programmer designed by MEAN WELL, and a personal computer are needed. Please contact MEAN WELL for details.

O Default 3 stage charging curve



Suitable for lead-acid batteries (flooded, Gel and AGM) and Li-ion batteries (lithium iron and lithium manganese).

© Embedded 3 stage charging curves


MODEL	Description	Vboost	Vfloat	CC(default)	
	Default, programmable	28.8	27.6		
241/	Pre-defined, gel battery	28	27.2	110A	
24V	Pre-defined, flooded battery	28.4	26.8		
	Pre-defined, AGM battery	29	27		
	Default, programmable	57.6	55.2		
48V	Pre-defined, gel battery	56	54.4	55A	
487	Pre-defined, flooded battery	56.8	53.6	SSA	
	Pre-defined, AGM battery	58	54		

Note:

When using this charger unit, please configured the system with recommended battery capacity defined by specification. Should battery capacity in use be much smaller so that user needs to set a low current for charging, under such condition it might cause higher current ripple.

3. Remote ON-OFF Control


The charger can be turned ON/OFF individually or along with other units in parallel by using the "Remote ON-OFF" function.




Between Remote ON-OFF and +5V-AUX	Charger Status
Switch Short	ON
Switch Open	OFF




- 5. Output Voltage Programming (or, PV / remote voltage programming / remote adjust / margin programming / dynamic voltage trim)
 - In addition to the adjustment via the built-in potentiometer, the output voltage can be trimmed to 75~125% of the nominal voltage by applying EXTERNAL VOLTAGE.







6. Output Current Programming (or, PC / remote current programming / dynamic current trim)

% The output current can be trimmed to 20~100% of the rated current by applying EXTERNAL VOLTAGE.






7. Temperature Compensation



- To exploit the temperature compensation function, please attach the temperature sensor, NTC, to the battery or the battery's vicinity.
- The charger is able to work normally without the NTC.





Input / Output Connector Pin No. Assignment(CN1): Positronic PCIM34W13M400A1

_	1 3 5 7 9 11 29 33	_	
		Mating Housing Positronic PCIM34W1	13F400A1
	2 4 6 8 10 13 31 32 34	-	

Pin No.	Function	Description		
1,2,3,4,6	-V	Negative output terminal.		
5,7,8,9,10	+V	Positive output terminal.		
11	+12V-AUX	Auxiliary voltage output, 10.8~13.2V, referenced to GND-AUX (pin 12). The maximum load current is 0.8A. This output has the built-in "Oring diodes" and is not controlled by the Remote ON/OFF control		
12	GND-AUX	Auxiliary voltage output GND. The signal return is isolated from the output terminals (+V & -V).		
13	+5V-AUX	Auxiliary voltage output, 4.5~5.5V, referenced to GND-AUX (pin 12). The maximum load current is 0.3A. This output has the built-in "Oring diodes" and is not controlled by the Remote ON/OFF control.		
14	SCL	For PMBus model: Serial Clock used in the PMBus interface. (Note.2)		
14	CANL	For CANBus model: Data line used in CANBus interface. (Note.2)		
15	SDA	For PMBus model: Serial Data used in the PMBus interface. (Note.2)		
15	CANH	For CANBus model: Data line used in CANBus interface. (Note.2)		
16	T-ALARM	High (4.5 ~ 5.5V): When the internal temperature exceeds the limit of temperature alarm, or when fan fails. Low (-0.1 ~ 0.5V): When the internal temperature is normal, and when fan works normally. The maximum sourcing current is 10mA and only for output(Note.2)		
17	Remote ON-OFF	The unit can turn the output ON/OFF by electrical signal or dry contact between <i>Remote ON/OFF</i> and +5V-AUX. (Note.2) Short (4.5 ~ 5.5V): Power ON; Open (-0.1 ~ 0.5V): Power OFF; The maximum input voltage is 5.5V.		
18	DC-OK	High $(4.5 \sim 5.5V)$: When the Vout \leq 16V/32V \pm 1V. Low $(-0.1 \sim 0.5V)$: When Vout \geq 16V/32V \pm 1V. The maximum sourcing current is 10mA and only for output. (Note.2) <i>DC OK</i> is associated with battery low protection.		
19	AC-OK	High (4.5 ~ 5.5V): When the input voltage is ≥87Vrms. Low (-0.1 ~ 0.5V): When the input voltage is ≤75Vrms. The maximum sourcing current is 10mA and only for output. (Note.2)		
20	D0	Interface lines for charging curve selection. (Note.1)		
21,22,23	A2,A1,A0	PMBus interface address lines. (Note.1)		
24,25	DB,DA	Differential digital signal for parallel control. (Note.1)		
26	PC	Connection for output current programming. (Note.1)		
27	PV	Connection for output voltage programming. (Note.1)		
28	+V(signal)	Positive output voltage signal. It cannot be connected directly to the load.		
29	-V(signal)	Negative output voltage signal. It is for certain function reference; it cannot be connected directly to the load.		
30	RTH+	To the state of th		
31	RTH-	Temperature sense associated with the temperature compensation function.		
32	FG	AC Ground connection.		
33	AC/L	AC Line connection.		
34	AC/N	AC Neutral connection.		
		•		

Note1: Non-isolated signal, referenced to [-V(signal)]. Note2: Isolated signal, referenced to GND-AUX.