

KERN DE12K1A

Langjähriges Erfolgsmodell mit staub- und spritzwassergeschütztem Auswertegerät



Measuring system

Adjustment options:	External calibration
Linearity:	3 g
Readout [d]:	1 g
Recommended adjusting weight:	12 kg (M1)
Reproducibility:	1 g
Resolution:	12000
Stabilisation time:	2,500 s
Warm up time:	30 min
Weighing range [Max]:	12 kg
Weighing system:	Strain gauge
Weighing units:	dwt g kg lb mo oz ozt tl (HK) tl (Tw) tol

Display

Display digit height:	2 cm
-----------------------	------

Counting

Counting resolution:	6000
Minimum piece weight at piece counting (Laboratory):	2 g
Minimum piece weight at piece counting (Normal):	20 g

Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	12 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	515 x 385 x 135 mm
Gross weight:	5,568 kg
Net weight:	4,755 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	1,400 m
Dimensions housing (WxDxH):	315 x 305 x 75 mm
Dimensions of display device (WxDxH):	225 x 110 x 60 mm
Dimensions of weighing plate (WxDxH):	318 x 308 x 75 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	315 x 305 mm