

Model Number

MLV41-LL-RT-IO/115/136

Fiber optic sensor


with 2 m fixed cable

Features

- Robust fiber optic sensor for reliable operation under all conditions
- Adjustable continuous sensitivity ٠
- Easy fiber optic installation with quick-٠ action clamping lock
- Aluminum housing with high-quality Delta Seal coating
- IO-link interface for service and pro-٠ cess data

Product information


The unique and extremely popular design of the MLV41 series enables it be mounted correctly in confined areas and offers all the functions that are normally only found on larger phototelectric sensors. The MLV41 series comes with a range of functions. For example, highly visible status LEDs on the front and back, resistance to ambient light, crosstalk protection and universally applicable output stages that permit every possible switching logic and polarity to be realized. The enhanced resistance to ambient light ensures reliable operation even where modern energy-saving lamps with electronic ballasts are in use. The same applies where multiple devices are present, i.e. the use of a number of sensors in the same vicinity causes no problems.



-+UB

BN


- ΒU






-0V

Indicators/operating means



Dimensions



Electrical connection

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

Pepperl+Fuchs Group www.pepperl-fuchs.com fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS 1

MLV41-LL-RT-IO/115/136

General specifications				
•			IODD Interpreter DTM	
Sensor range	on	ı black (6 %): up to 36mm ı Kodak white, reflection factor 90% up to 120mm th LLR 04-1.6-0.5-WC3 fiberoptic cable	Software for the integration of IODDs in a frame application (e. g. PACTware)	
Adjustment range		120 mm on Kodak white, reflection factor 90%	IO-Link-Master02-USB	
Reference target		00 mm x 100 mm on Kodak white, reflection factor 90%	IO-Link master, supply via USB port or se-	
Light source	LE		parate power supply, LED indicators, M12	
Light type		odulated visible red light , 660 nm	plug for sensor connection	
Functional safety related param		70 a		
MTTF _d Mission Time (T _M)	20		OMH-41	
Diagnostic Coverage (DC)	0 9		Mounting bracket	
Indicators/operating means			LCR 04-1,6-0,5-Z1	
Operation indicator	Gr fla	ED green, statically lit Power on , Undervoltage indicator: reen LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green ishing (approx. 4 Hz) , IO link communication: green LED res out briefly (1 Hz)	Glass fiber optic - diffuse with PVC co- vering	
Function indicator	LE	ED yellow, lights up with receiver lit ; flashes when falling short the stability control	LLR 04-1,6-0,5-G(M6x30) Glass fiber optic - diffuse with metal silico- ne covering	
Control elements	se	ensitivity adjustment		
Electrical specifications				
Operating voltage	U _B 10) 30 V DC	LCR 04-1,6-0,5-WC 3 Glass fiber optic - diffuse with PVC co- vering	
Ripple		ax. 10 %		
No-load supply current	l _o ma	ax. 40 mA		
Interface			LLR 04-1,6-0,5-W C3	
Interface type		-Link	Glass fiber optic - diffuse with metal silico- ne covering	
Protocol		-Link V1.0		
Mode	CC	OM 2 (38.4 kBaud)	C C	
Output Switching type	lig	ht/dark on	LCE 04-1,6-1,0-Z1 Glass fiber optic - thru-beam with PVC co-	
Signal output		push-pull (4 in 1) outputs, complementary, short-circuit proof, verse polarity protected	vering	
Switching voltage	ma	ax. 30 V DC	LCE 04-1,6-1,0 G Glass fiber optic - thru-beam with PVC co- vering	
Switching current	ma	ax. 100 mA		
Voltage drop	u	2.5 V DC		
Switching frequency		000 Hz	LLE 04-1,6-1,0-G	
Response time	0.3	5 ms	Glass fiber optic - thru-beam with metal si-	
Ambient conditions Ambient temperature	-20	0 60 °C (-4 140 °F)	licone covering	
Storage temperature		0 75 °C (-40 167 °F)		
Mechanical specifications			LCE 04-1,6-1,0-W C3 Glass fiber optic - thru-beam with PVC co-	
Housing width	31	mm		
Housing height	56	0.5 mm	vering	
Housing depth	13	8.6 mm	LLE 04-1,6-1,0-W C3	
Fiber optic adapter	04	l de la companya de l	Glass fiber optic - thru-beam with metal si-	
Degree of protection	IP	67	licone covering	
Connection Material	2 r	m fixed cable , 5-pin	MLV41-LL IODD	
Housing		uminum, Delta-Seal coated	IODD for communication with MLV41-LL- IO-Link sensors	
Optical face		ber optic connection		
Mass	50) g	Other suitable accessories can be found at	
Compliance with standards and ves	d directi-		www.pepperl-fuchs.com	
Directive conformity			hold a second	
EMC Directive 2004/108/EC	FN	N 60947-5-2:2007		
Standard conformity				
Product standard		N 60947-5-2:2007 C 60947-5-2:2007		
Approvals and certificates				
Protection class		, rated voltage ≤ 50 V AC with pollution degree 1-2 according b IEC 60664-1 functional insulation acc. to DIN EN 50178		
UL approval	c	ULus Listed 57M3 (Only in association with UL Class 2 power upply; Type 1 enclosure)		
CCC approval		CCC approval / marking not required for products rated ≤36 V		
IO link function				
The IO link operating mode is indicated by the green LED indicator with a short interruption				
	ation simulta to requireme	aneously provides process data (measurement data ent data.		

Identification:

- Manufacturer information
- Product ID

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com Release date: 2017-05-03 14:23 Date of issue: 2017-05-03 249790_eng.xml

2

User-specific ID

Device parameters:

- · Teach-in parameters
- Operating parameters
- Configuration parameters
- Device commands

Diagnostic messages and warnings

Setting information

Detection range adjustment:

The detection range can be set via the rotary switch or the IO-Link.

Setting using the rotary switch:

- If you would like to change the detection range on the sensor, turn:
- the rotary switch to the left to reduce the value.
- the rotary switch to the right to increase the value.

With the IO-Link, the set detection range the current rotary switch configuration is always assigned. If the rotary switch is too far to the left or the right, perform the following:

Turn the potentiometer completely to the left until it stops. The LED will briefly flash green. The assignment of the current rotary switch configuration to the detection range set via IO-Link is overridden. Now set the desired detection range again.

Example application - manually reduce detection range:



The potentiometer has one position as shown here. The adjustable detection range is set via IO-Link to maximum. The rotary switch is too far to the left to set a considerably lower detection range for example.



Turn the potentiometer to the left until it stops to override the set value to this rotary switch configuration. The LED will briefly flash green.



Now set the desired detection range again.

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

