

# KERN TAB20-3

Hochpräzise Taschenkaratwaage für Juweliere und Reisende



## Service

Adjustment at the location of installation: 961-247

DAkKS Certificate: 963-127

## Category

Brand: KERN

Category: Balances

Product Group: Pocket balance

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 188 x 120 x 44 mm

Gross weight: 314 g

Net weight: 170 g

Shipping method: Parcel service

## Construction

Casing material: Plastic

Dimensions draft shield (WxDxH): 94 x 100 x 12 mm

Material weighing plate: Plastic

Overall dimensions mounted (WxDxH): 95 x 135 x 33 mm

Weighing space (WxDxH): 90 x 90 x 10 mm

Weighing surface (d): 18

## Measuring system

Adjustment options: External calibration

Linearity: 4 mg

Readout [d]: 1 mg

Recommended adjusting weight: 10 g (F2)

Reproducibility: 2 mg

Resolution: 20000

Stabilisation time: 3 s

Tare range: -20000 mg

Warm up time: 30 min

Weighing range [Max]: 20 g

Weighing system: Strain gauge

Weighing units: ct g gn

## Display

Display digit height: 9 mm

## Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 30 °C

Minimum ambient temperature: 10 °C

Minimum humidity: 15 %

## Power supply

Operating time: 150 h