**Dimensions** 

CE (Սլ **O**IO-Link US

# **Model Number**

## OBT600-R200-2EP-IO-V31-L

Triangulation sensor (BGS) with 4-pin, M8 x 1 connector

#### **Features**

- Medium design with versatile • mounting options
- DuraBeam Laser Sensors durable ٠ and employable like an LED
- Extended temperature range • -40°C ... 60°C
- High degree of protection IP69K
- IO-link interface for service and process data

## **Product information**


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design-from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link.


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and

can be adapted to the application environment.



## **Electrical connection**




## Pinout



in accordance with EN 60947-5-2 (brown) (white) (blue) (black) BN BN BU BK

# Indicators/operating means



1	Sensitivity adjustment	
2	Light-on / dark-on changeover switch	
3	Operating indicator / dark on	GN
4	Signal indicator YE	
5	Operating indicator / light on	GN



USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Laserlabel

#### **Technical data**

#### General specifications Detection range Detection range min. Detection range max. Adjustment range Reference target Light source Light type Laser nominal ratings Note Laser class Wave length Beam divergence Pulse length Repetition rate max. pulse energy Black/White difference (6 %/90 %) Diameter of the light spot Angle of divergence Ambient light limit Functional safety related parameters MTTF<sub>d</sub> Mission Time (T<sub>M</sub>) Diagnostic Coverage (DC) Indicators/operating means

Operation indicator

Function indicator

Control elements Control elements **Electrical specifications** Operating voltage Ripple No-load supply current Protection class

Interface Interface type Device profile

Transfer rate **IO-Link Revision** Min. cycle time Process data witdh

SIO mode support Device ID Compatible master port type Output

Switching type

Signal output

Switching voltage Switching current Usage category Voltage drop Switching frequency Response time

Conformity Communication interface Product standard Laser safety

Ambient conditions Ambient temperature

Storage temperature **Mechanical specifications** Housing width

40 ... 600 mm 40 ... 90 mm 40 ... 600 mm 90 ... 600 mm standard white, 100 mm x 100 mm laser diode modulated visible red light

LASER LIGHT , DO NOT STARE INTO BEAM

680 nm > 5 mrad, d63 < 2,8 mm in the range of 350 mm ... 800 mm 3μs approx. 13 kHz 10.4 nJ < 5 % at 300 mm approx. 2.5 mm at a distance of 600 mm approx. 0.3 EN 60947-5-2 : 70000 Lux

560 a

UB

 $I_0$ 

Ud

20 a

0%

LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode LED yellow: constantly on - object detected constantly off - object not detected Light-on/dark-on changeover switch Sensing range adjuster

10 ... 30 V DC max. 10 % < 15 mA at 24 V supply voltage Ш

IO-Link (via C/Q = pin 4) Identification and diagnosis Smart Sensor type 2.4 COM 2 (38.4 kBaud) 1.1 2.3 ms Process data input 1 Bit Process data output 2 Bit ves 0x111603 (1119747) A

The switching type of the sensor is adjustable. The default setting is: $C/Q - Pin4$ : NPN normally open / light-on, PNP normally closed dark-on, IO-Link /Q - Pin2: NPN normally closed / dark-on, PNP normally open / light-on
2 push-pull (4 in 1)outputs, short-circuit protected, reverse polarity protected, overvoltage protected
max. 30 V DC
max. 100 mA , resistive load
DC-12 and DC-13
$\leq$ 1.5 V DC
1650 Hz
300 µs
IEC 61131-9
EN 60947-5-2
EN 60825-1:2014
-40 60 °C (-40 140 °F)
-40 70 °C (-40 158 °F)



IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

## Accessories

#### IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

## V31-GM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

## V31-WM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

15 mm

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

1/





Housing height	50.6 mm			
Housing depth	41.7 mm			
Degree of protection	IP67 / IP69 / IP69K			
Connection	4-pin, M8 x 1 connector, 90° rotatable			
Material				
Housing	PC (Polycarbonate)			
Optical face	PMMA			
Mass	approx. 35 g			
Approvals and certificates				
UL approval	E87056 , cULus Listed , class 2 power supply , type rating 1			

CCC approval FDA approval

CCC approval / marking not required for products rated ≤36 V IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

# **Curves/Diagrams**






Release date: 2018-05-22 17:13 Date of issue: 2018-09-10 295670-100225\_eng.xml

www.pepperl-fuchs.com





To unlock the adjustment functions, rotate the sensing range/sensitivity adjuster by more than 180°.

## Sensing Range/Sensitivity

To increase the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster clockwise.

To reduce the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster counter-clockwise.

As soon as the end of the adjustment range is reached, the signal indicator flashes at 8 Hz.

#### **Configuring Light On/Dark On**

Press the light-on/dark-on changeover switch for more than 1 second (but less than 4 seconds). "Light on/dark on" mode changes and the relevant operating indicator lights up.

If you press the light-on/dark-on changeover switch for longer than 4 seconds, the "light on/dark on" mode will switch back to the original setting. The current status is activated when the light-on/dark-on changeover switch is released.

#### **Restoring Factory Settings**

Press the light-on/dark-on changeover switch for more than 10 seconds (but less than 30 seconds) until all LEDs go out. When the light-on/dark-on changeover switch is released, the signal indicator lights up. After 5 seconds, the sensor resumes operation with the factory settings.

The adjustment functions are locked after 5 minutes of inactivity. To unlock the adjustment functions, rotate the sensing range/ sensitivity adjuster again by more than 180°.

Δ

