



Model Number

ML100-8-H-350-RT/103/115b

Background suppression sensor with fixed cable and M12 connector, 4-pin


Features


- Miniature design •
- Easy to use •
- Very bright, highly visible light spot •
- Full metal thread mounting •
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light ٠

Product information


The ML100 series is characterized by its miniature housing with integral, all-metal threaded bushings. All versions are equipped with a visible red transmitter LED. This greatly simplifies installation and commissioning. The switching states are easily visible from all directions thanks to the highly visible LEDs.

Dimensions






Electrical connection







Indicators/operating means



_		
1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display	yellow
4	Operating display	green

Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



ML100-8-H-350-RT/103/115b

General specifications			
Detection range		5 350 mm	
Detection range min.		5 30 mm	
Detection range max.		5 350 mm	
Adjustment range		30 350 mm	
Reference target		standard white, 100 mm x 100 mm	
Light source		LED	
Light type		modulated visible red light	
Polarization filter		no	
Black/White difference (6 %/90	%)	< 18 % at 350 mm	
Diameter of the light spot	,,	approx. 20 mm at a distance of 350 mm	
Angle of divergence		approx. 4 °	
Optical face		frontal	
Ambient light limit		EN 60947-5-2:2007+A1:2012	
	neters		
Functional safety related parameters		860 a	
MTTF _d Mission Time (T_)		20 a	
Mission Time (T _M) Diagnostic Coverage (DC)		20 a 0 %	
		0.70	
Indicators/operating means			
Operation indicator		LED green: power on	
Function indicator		LED yellow: lights when object is detected	
Control elements		Sensing range adjuster	
Control elements		Light-on/dark-on changeover switch	
Electrical specifications			
Operating voltage	UB	10 30 V DC	
Ripple		max. 10 %	
No-load supply current	I ₀	< 20 mA	
Output			
Switching type		The switching type of the sensor is adjustable. The defau ting is: light on	
Signal output		1 PNP output, short-circuit protected, reverse polarity pro open collector	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA , resistive load	
Voltage drop	U _d	≤ 1.5 V DC	
Switching frequency	f	500 Hz	
Response time		1 ms	
Ambient conditions			
Ambient temperature		-30 60 °C (-22 140 °F)	
Storage temperature		-40 70 °C (-40 158 °F)	
Mechanical specifications			
Degree of protection		IP67	
Connection		300 mm fixed cable with 4-pin, M12 x 1 connector	
Material			
Housing		PC (Polycarbonate)	
Optical face		PMMA	
Mass		approx. 20 g	
Tightening torque, fastening scr	ews	0.6 Nm	
Cable length		0.3 m	
Compliance with standards an ves	d direct	i-	
Directive conformity			
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012	
Standard conformity			
Standards		UL 60947-5-2	
Gianuarus			
Approvals and certificates			
UL approval		cULus Listed, Class 2 Power Source or listed Power Sup with a limited voltage output with (maybe integrated) fus (max. 3.3 A according UL248), Type 1 enclosure	
CCC approval		CCC approval / marking not required for products rated :	

Accessories OMH-ML100-01 Mounting aid for ML100 series, Mounting bracket OMH-ML100-02 Mounting aid for ML100 series, Mounting bracket OMH-ML100-03 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm OMH-ML100-04 Mounting aid for ML100 series, Mounting bracket OMH-ML100-05 Mounting aid for ML100 series, Mounting bracket OMH-F10-ML100 Mounting aid for ML100 series **OMH-10** Mounting aid OMH-ML100-S1 Mounting bracket OMH-ML100-08 fault set-Mounting aid for ML100 series, Snap-in protected, Other suitable accessories can be found at www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001

www.pepperl-fuchs.com


2


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Curves/Diagrams





Release date: 2016-07-06 08:18 Date of issue: 2016-07-06 225030_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001

www.pepperl-fuchs.com

