

# PRODUCT SPECIFICATION

Rechargeable Lithium Ion Battery

Model : INR21700 M50 18.2Wh



## Contents

<b>Contents</b> .....	<b>3</b>
<b>1. General Information</b> .....	<b>4</b>
1.1 Scope	
1.2 Product Classification	
1.3 Model Name	
<b>2. Nominal Specification</b> .....	<b>4</b>
2.1 Energy	
2.2 Nominal Voltage	
2.3 Nominal Shipping SOC	
2.4 Standard Charge	
2.5 Max. Charge Voltage	
2.6 Standard Discharge	
2.7 Operating Temperature	
2.8 Storage Temperature (for shipping state)	
2.9 Weight	
<b>3. Appearance and Dimension</b> .....	<b>5</b>
3.1 Appearance	
3.2 Dimension	
<b>4. Performance Specification</b> .....	<b>6</b>
4.1 Standard Test Condition	
4.2 Electrical Specification	
4.3 Environmental Specification	
4.4 Safety Specification	
<b>5. Caution</b> .....	<b>10</b>
5.1 Cautions for Use and Handling	
5.2 Prohibitions	
5.3 Caution for the battery and the pack	
<b>6. Exclusion of Liability</b> .....	<b>13</b>

## 1. General Information

### 1.1 Scope

This product specification defines the requirements of the rechargeable lithium ion battery to be supplied to the Customer by LG Chem.

1.2 Product classification : Cylindrical rechargeable lithium ion battery

1.3 Model name : INR21700 M50

## 2. Nominal Specification

Item	Condition / Note	Specification
2.1 Energy	Std. charge / discharge	Nominal 18.2Wh Minimum 17.6Wh
2.2 Nominal Voltage	Average	3.63V
2.3 Nominal Shipping SOC		30%
2.4 Standard Charge (Refer to 4.2.1)	Constant current Constant voltage End current(Cut off)	0.3C (1,455mA) 4.2V 50mA
2.5 Max. Charge Voltage		4.20V
2.6 Standard Discharge (Refer to 4.1.2)	Constant current End voltage(Cut off)	0.2C (970mA) 2.50V
2.7 Operating Temperature	Charge Discharge  This condition does not affect the safety, but it is only possible to drive (charge and discharge) and does not guarantee cycle performance.	0~45℃ -20~55℃

2.8 Storage Temperature (for shipping state)	1 month	-20 ~ 55℃
	3 months	-20 ~ 45℃
	1 year	-20 ~ 25℃
	Recovery energy after the storage ≥ 80% of minimum energy	
2.9 Weight	Without washer	68.5 ± 1.0 g

\* Recovery Energy: After storage, cells shall be discharged with std. discharge condition (4.1.2), and then cells shall be charged with std. charge condition (4.1.1), and then discharged with Std. condition (4.1.2).

### 3. Appearance and Dimension

#### 3.1 Appearance

There shall be no such defects as deep scratch, crack, rust, discoloration or leakage, which may adversely affect the commercial value of the cell.

#### 3.2 Dimension

Diameter : ≤ 21.10 mm

Diameter is defined as the largest data value measured on the "A" area of a cylindrical cell

Height : ≤ 70.15 mm



## 4. Performance Specification

### 4.1 Standard Test Condition

#### 4.1.1 Standard Charge

Unless otherwise specified, "Standard Charge" shall consist of charging at constant current of 0.3C. The cell shall then be charged at constant voltage of 4.20V while tapering the charge current. Charging shall be terminated when the charging current has tapered to 50mA. For test purposes, charging shall be performed at 25°C ± 2°C.

#### 4.1.2 Standard Discharge

"Standard Discharge" shall consist of discharging at a constant current of 0.2C to 2.50V. Discharging is to be performed at 25 °C ± 2 °C unless otherwise noted (such as capacity versus temperature).

#### 4.1.3 Charge / discharge condition (I)

Cells shall be charged at constant current of 0.33C to 4.20V with end current of 1/20C. Cells shall be discharged at constant current of 0.33C to 2.85V. Cells are to rest 10 minutes after charge and 20 minutes after discharge at 25 °C ± 2 °C.

### 4.2 Electrical Specification

Item	Condition	Specification
4.2.1 Initial AC Impedance	Cell shall be measured at 1kHz after charge per 4.1.1.	≤ 25 mΩ
4.2.2 Initial DC Resistance	Cell shall be charged per 4.1.1 and discharged to the SOC (states of charge) 50%. Measurement of internal impedance under DC loads at constant current of 0.5C for 30 sec at 25 °C ± 2 °C.	30 ± 6 mΩ
4.2.3 Initial Energy	Cells shall be charged per 4.1.1 and discharged per 4.1.2 within 1h after full charge.	≥ 17.6 Wh
4.2.4 Cycle Life	Cells shall be charged and discharged per 4.1.3 for 500 cycles. A cycle is defined as one charge and one discharge. 501st discharge energy shall be measured per 4.1.1 and 4.1.2.	≥ 80% (of Wh <sub>min</sub> in 2.1)
4.2.5 I <sub>max</sub> for Charge	At each SOC(states of charge) state, the charge cut off reaches 4.20V.	Refer to table A.

4.2.6 $I_{\max}$ for Discharge	At each SOC(states of charge) state, the discharge cut off reaches 2.50V.	Refer to table B.
4.2.7 Max. Charge Current(Continuous)	0 ~ 25 °C	0.3C (1,455mA)
	25 ~ 45 °C	0.7C (3,395mA)
4.2.8 Max. Pulse Discharge Power	Pulse Power(10sec), 25 °C ± 2 °C	80W (SOC 80%)
4.2.9 Max. Discharge Current(Continuous)	-20 ~ 10 °C	0.5C (2,425mA)
	10 ~ 25 °C	3.0C(14,550mA)
	25 ~ 55 °C	1.5C (7,275mA)

Table A.  $I_{max}$  for Charge

Unit: A

	Temp.	Time	SOC100	SOC90	SOC80	SOC70	SOC60	SOC50	SOC40	SOC30	SOC20	SOC10	SOC5
	$I_{max}$ for Charging	-20°C	2sec	-	-	-	-	-	2.5	2.5	2.5	2.5	2.5
10sec			-	-	-	-	-	2.5	2.5	2.5	2.5	2.5	2.5
30sec			-	-	-	-	-	-	2.5	2.5	2.5	2.5	2.5
-10°C		2sec	-	-	-	2.5	2.5	5	6	6	7	8	9
		10sec	-	-	-	2.5	2.5	5	6	6	7	7	8
		30sec	-	-	-	2.5	2.5	5	5	6	7	7	7
0°C		2sec	-	2.5	2.5	6	9	11	12	13	15	16	18
		10sec	-	-	2.5	6	8	10	11	12	14	14	15
		30sec	-	-	2.5	5	7	9	10	11	13	13	13
10°C		2sec	-	2.5	5	8	11	14	16	17	19	19	22
		10sec	-	2.5	5	7	10	13	14	15	18	17	19
		30sec	-	2.5	2.5	6	8	11	13	14	15	15	16
24°C		2sec	-	4	6	10	13	17	19	21	24	24	26
		10sec	-	3	6	9	12	15	18	19	22	21	22
		30sec	-	2.5	5	8	10	13	15	17	19	19	18
40°C		2sec	-	2.5	7	11	15	19	21	23	27	29	32
		10sec	-	2.5	7	10	13	17	19	21	25	25	26
		30sec	-	2.5	6	9	11	15	17	19	22	21	21
55°C		2sec	-	2.5	8	12	16	20	22	25	29	33	37
		10sec	-	2.5	7	11	14	18	20	22	27	27	29
		30sec	-	2.5	6	9	12	16	18	20	23	22	22

 Table B.  $I_{max}$  for Charge

Unit: A

	Temp.	Time	SOC100	SOC90	SOC80	SOC70	SOC60	SOC50	SOC40	SOC30	SOC20	SOC10	SOC5
	$I_{max}$ for Discharging	-20°C	2sec	12	11	10	10	8	7	6	2.5	-	-
10sec			11	9	9	8	7	6	5	2.5	-	-	-
30sec			9	8	7	7	6	6	5	2.5	-	-	-
-10°C		2sec	21	18	18	17	16	14	13	12	7	2.5	-
		10sec	20	17	16	15	14	13	12	11	6	-	-
		30sec	20	16	16	14	13	12	11	10	5	-	-
0°C		2sec	34	35	35	33	30	28	25	21	16	6	2.5
		10sec	33	34	32	31	28	23	22	19	13	2.5	-
		30sec	33	31	29	27	22	21	20	17	10	2.5	-
10°C		2sec	42	43	42	40	37	34	32	29	23	11	6
		10sec	40	40	38	36	34	31	29	25	20	7	2.5
		30sec	38	36	34	32	29	26	24	22	16	5	-
24°C		2sec	53	53	51	48	45	41	38	35	31	20	12
		10sec	49	48	46	44	40	37	35	32	28	15	8
		30sec	46	44	41	39	36	33	30	27	22	11	5
40°C		2sec	59	58	54	52	48	44	41	38	33	25	18
		10sec	53	52	49	47	43	40	37	34	29	19	13
		30sec	49	46	43	41	38	35	32	28	24	15	9
55°C		2sec	61	59	56	53	49	45	42	38	34	25	19
		10sec	56	54	51	48	44	41	38	34	28	19	14
		30sec	51	48	45	42	39	36	33	29	24	15	8



## 4.3 Environmental Specification.

Item	Condition		Specification
4.3.1 High Temperature Storage Test	Cells shall be charged per 4.1.1 and stored in a temperature-controlled environment at 55°C for 1 week. Recovery Energy: After storage, cells shall be discharged with std. discharge condition (4.1.2), and then cells shall be charged with std. charge condition (4.1.1), and then discharged with Std. condition (4.1.2).		Energy recovery rate ≥ 80% (Wh <sub>min</sub> in 2.1)
4.3.2 Temperature Dependency of Capacity	Cells shall be charged per 4.1.1 at 25°C ± 2°C and discharged per 4.1.2 at the following temperatures.		
	Charge	Discharge	Energy
	25°C	-10°C 0°C 25°C 55°C	≥70% of Wh <sub>min</sub> ≥80% of Wh <sub>min</sub> ≥100% of Wh <sub>min</sub> ≥95% of Wh <sub>min</sub>

## 4.4 Safety Specification

UN38.3

## 5. Caution

Warning for using the lithium ion rechargeable battery. Mishandling of the battery may cause heat, fire and deterioration in performance. Be sure to observe the following.

### 5.1 Cautions for Use and Handling

- When using the application equipped with the battery, refer to the user's manual before usage.
- Please read the specific charger manual before charging.
- Charge time should not be longer than specified in the manual.
- When the cell is not charged after long exposure to the charger, discontinue charging.
- Battery must be charged at operating temperature range 0 ~ 45°C.
- Battery must be discharged at operating temperature range -20 ~ 60°C.
- Please check the positive(+) and negative(-) direction before packing.
- When a lead plate or wire is connected to the cell for packing, check out insulation not to short-circuit.
- Battery must be stored separately.
- Battery must be stored in a dry area with low temperature for long-term storage.
- Do not place the battery in direct sunlight or heat.
- Do not use the battery in high static energy environment where the protection device can be damaged.
- When rust or smell is detected on first use, please return the product to the seller immediately.
- The battery must be away from children or pets
- When cell life span shortens after long usage, please exchange to new cells.
- Do insulate between the metal plate and cell or other components not to make a electrical short.
- When use cells for an assembly of module or pack, the "first-in, first-out" (FIFO) principle should be applied
- The cells should be handled and used in Pack/System manufacturing companies only.
- The cells should be sold only to Battery Pack Maker(s) or System Integrator(s). The cells should not be handled by individual consumers and should not be sold to individual consumers by individual markets. (especially, the cells are strictly prohibited to be used for any kinds of E-cigarette devices).
- Be sure to request and confirm the most current product specifications in advance which explain the specifications in detail, before the final stage of your design, purchasing or use for any application.

### 5.2 Prohibitions

- Do not use different charger. Do not use cigarette jacks (in cars) for charging.
- Do not charge with constant current more than maximum charge current.
- Do not disassemble or reconstruct the battery.
- Do not throw or cause impact.
- Do not pierce a hole in the battery with sharp things. (such as nail, knife, pencil, drill)

- 
- Do not use with other batteries or cells.
  - Do not solder on battery directly.
  - Do not press the battery with overload in manufacturing process, especially ultrasonic welding.
  - Do not use old and new cells together for packing.
  - Do not expose the battery to high heat. (such as fire)
  - Do not put the battery into a microwave or high pressure container.
  - Do not use the battery reversed.
  - Do not connect positive(+) and negative(-) with conductive materials (such as metal, wire)
  - Do not allow the battery to be immersed in or wetted with water or sea-water.

### 5.3 Caution for the battery and the pack

Pack shall meet under condition to maintain battery safety and last long performance of the lithium rechargeable cells.

#### 5.3.1 Installing the battery into the pack

- . The cell should be inspected visually before battery assembly into the pack.
- . Damaged cell should not be used. (damaged surface, can-distortion, electrolyte-smell)
- . Different Lot Number cells should not be packaged into the same pack.
- . Different types of cells, or same types but different cell maker's should not be used together.

#### 5.3.2 Design of battery pack

- . The battery pack should not be connected easily to any charger other than the dedicated charger.
- . The battery pack has function not to cause external short cut easily.
- . The design of battery pack and its structure should be reviewed physically, mechanically and electrically not to cause cell imbalance.
- . The battery pack for multiple cells should be designed to monitor the voltage of each bank.

#### 5.3.3 Charge

- . Charging method is Constant Current-Constant Voltage (CC/CV).
- . Charging should be operating under maximum charge voltage and current which is specified in the product specification. (Article. 2.4, 2.5)
- . The battery should be charged under operating temperature specified in the product specification. (Article. 2.9)

#### 5.3.4 Discharge

- . Discharging method is Constant Current (CC).

---

(In case of using the battery for mobile equipment, discharging mode could be Constant Power.)

- Discharging should be operating under maximum discharge current which is specified in the product specification. (Article. 2.7)
- Discharging should be done by cut off voltage which is specified in the product specification. (Article. 2.6)
- The battery should be discharged under operating temperature specified in the product specification. (Article. 2.9)

#### 5.3.5 Protection Circuit

- When battery packs for any applications are assembled with cells, following functions must be designed into the battery packs and/or in the charger or charging adapter. The detailed levels, values, conditions for each following functions should be referring to the contents specified in this Product Specification. If one or more than one function is/are to be omitted, the Packer Company (and/or System integration company) must be informing to LG Chem's or to LG Chem's sales Agent company. Without informing to LGC, LGC will not be liable for any field quality issues happened due to exclusion of following functions.

- (1) Over voltage protection circuit
- (2) Under voltage protection circuit
- (3) Over Charge current protection circuit
- (4) Over Discharge current protection circuit
- (5) Short circuit protection
- (6) Over Temperature protection circuit
- (7) 2nd over voltage protection
- (8) FET failure protection (in case FET is out of order)
- (9) Cell imbalance protection circuit (only for battery packs assembled with more than one cell)
- (10) Cell Voltage balancing function (only for battery packs assembled with more than one cell)

## 6. Exclusion of Liability

The warranty shall not cover defects caused by normal wear and tear, inadequate maintenance, handling, storage, faulty repair, modification to the battery or pack by a third party other than LGC or LGC's agent approved by LGC, Failure to observe the product specification provided herein or improper use of installation, including but not limited to, the following:

- Damage during transport or storage
- Incorrect installation of battery into pack or maintenance
- Use of battery or pack in inappropriate environment
- Improper, inadequate, or incorrect charge, discharge or production circuit other than stipulated herein
- Incorrect use or inappropriate use
- Insufficient ventilation
- Ignoring applicable safety warnings and instructions
- Altering of attempted repairs by unauthorized personnel
- In case of force majeure (Ex. Lightning, Storm, Flood, fire, Earthquake, Etc)

There are no warranties – Implied or express – Other than those stipulated herein. LG chem. Shall not be liable for any consequential or indirect damages arising of in connection with the product specification, battery or pack.