













Model Number


MLV12-54-LAS-300/76b/95/110

Retroreflective sensor with 4-pin M8 connector, 90° adjustable position


Features

- Series of sensors in a widely used standard housing
- Visible red light, pulsed LASER light
- Precision: high degree of repeatability thanks to small light spot
- Reliable detection of minimum target sizes > 0.3 mm
- Resistant against noise: reliable operation under all conditions
- High level of stability thanks to the metal housing frame

Dimensions



Electrical connection




- O = Light on
- = Dark on

Pinout



Indicators/operating means





| Technical data | | |
|----------------------------------|----------------|--|
| General specifications | | |
| Effective detection range | | 100 450 mm |
| Reflector distance | | 0.02 4 m |
| Threshold detection range | | 5.6 m |
| Reference target | | MH82 reflector |
| Light source | | laser diode |
| Light type | | modulated visible red light |
| Laser nominal ratings | | modulated visible red light |
| Note | | LASER LIGHT , DO NOT STARE INTO BEAM |
| Laser class | | 1 |
| Wave length | | 650 nm |
| Beam divergence | | 2 mrad |
| Pulse length | | 1.8 μs |
| Repetition rate | | 17.86 kHz |
| max. pulse energy | | 1.1 nJ |
| Target size | | > 0.3 mm |
| Diameter of the light spot | | approx. 0.5 mm at detection range 150 mm up to 400 mm |
| Angle of divergence | | 0.1° |
| Ambient light limit | | |
| Continuous light | | 50000 Lux |
| Modulated light | | 5000 Lux |
| Functional safety related parame | eters | |
| MTTF _d | | 930 a |
| Mission Time (T _M) | | 10 a |
| Diagnostic Coverage (DC) | | 90 % |
| Indicators/operating means | | |
| Operating display | | LED green, flashes in case of short-circuit |
| Function display | | 2 LEDs yellow, light up when light beam is free, flash when falling |
| . and an anoptaly | | short of the stability control, off when light beam is interrupted |
| Controls | | rotary switch for light/dark, sensitivity adjuster |
| Electrical specifications | | |
| Operating voltage | U _B | 10 30 V DC |
| Ripple | | max. 10 % |
| No-load supply current | I _O | max. 40 mA |
| Input | | |
| Test input | | emitter deactivation at 0 V |
| Output | | |
| Switching type | | light/dark on switchable |
| Signal output | | 1 push-pull (4 in 1) output, short-circuit protected, reverse pola- |
| 3 | | rity protected |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 0.1 A |
| Voltage drop | U _d | ≤ 2.5 V DC |
| Switching frequency | f | 2500 Hz |
| Response time | | 0.2 ms |
| Ambient conditions | | |
| Ambient temperature | | -10 50 °C (14 122 °F) |
| Storage temperature | | -20 65 °C (-4 149 °F) |
| Mechanical specifications | | |
| Protection degree | | IP67 |
| Connection | | 4-pin M8 metal connector, 90° rotatable |
| Material | | |
| Housing | | Frame: nickel plated, die cast zinc, |
| - | | Laterals: glass-fiber reinforced plastic PC |
| Optical face | | Plastic pane |
| Mass | | 60 g |
| Compliance with standards and | directi- | • |
| ves | | |
| Standard conformity | | |
| Product standard | | EN 60947-5-2:2007 |
| Chook and impost a sister. | | IEC / EN 60069, helf sine, 40 g in each X, X and Z directions |
| Shock and impact resistance | | IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions |
| Vibration resistance | | IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions |
| | | a ooono |
| Laser class | | IEC 60825-1:2007 Complies with 21 CFR 1040 10 and 1040 11 |
| Laser class | | IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated |
| Laser class | | |
| | | except for deviations pursuant to Laser Notice No. 50, dated |
| Approvals and certificates | | except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007 |
| | | except for deviations pursuant to Laser Notice No. 50, dated |

Accessories

OMH-MLV12-HWG

Mounting bracket for series MLV12 sensors

OMH-MLV12-HWK

Mounting bracket for series MLV12 sensors

OMH-K01

dove tail mounting clamp

OMH-K02

dove tail mounting clamp

OMH-K03

dove tail mounting clamp

OMH-01

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

OMH-06

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

Reflector with Micro-structure, rectangular 82 mm x 60 mm, mounting holes

REF-MH50

Reflector with Micro-structure, rectangular 50.9 mm x 50.9 mm, mounting holes, fixing strap

REF-MH78

Reflector with Micro-structure, hexagonal 78 mm x 61 mm, mounting holes

REF-MH20

Reflector with Micro-structure, rectangular 32 mm x 20 mm, mounting holes

REF-MA21

Reflector with Micro-structure, round ø 21 mm, self-adhesive

OFR-MCS-A4

Reflective tape A4 (297 mm x 210 mm)

OFR-MCS-400/18


Reflective tape, cut to size

Other suitable accessories can be found at www.pepperl-fuchs.com


PEPPERL+FUCHS

Date of issue: 2013-05-13 128106_eng.xml

2



Curves/Diagrams



Laser notice laser class 1

- The irradiation can lead to irritation especially in a dark environment. Do not point at people!
- Maintenance and repairs should only be carried out by authorized service personnel!
- Attach the device so that the warning is clearly visible and readable.
- The warning accompanies the device and should be attached in immediate proximity to the device.
- Caution Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.