

Supplier	Article description	Art. No. / GTIN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Drainage submersible pump I-Compac 13000	30191	24 Months	
		4011458301911		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	
46,0	38,3	38,0	23,5	pack. Unit (pcs.) 4
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	Qty.
Width	Depth	Height		
22,0	18,0	36,0	5,2 / 5,6	1

Drainage submersible pump
I-Compac 13000

quantity / pallet:
quantity / truck:

Description:

Specially designed for dirty water drainage submersible pump with vertical pump outlet and integrated float switch, for use in drainage shafts. This pump can be switched from automatic to manual operation.
Can also be used for polluted water to 16 mm grain size.

Technical Data:

Nominal performance: 750 Watt
Mains Voltage / Frequency: 230 V~ / 50 Hz
Delivery height / pressure max.: 9 m / 0.9 bar
Flow rate max.: 216 l/min 13,000 l/h
Pump housing: Plastic
Pressure port: 47.8 mm (1½" male)
Max. fluid temp.: 35° C
Power cord: 10 m / H07RN8-F
Grain size max.: 16 mm
Submersion depth max.: 7 m
Suction level min.: 25 mm

Scope of delivery:

- MultiDimension fitting: 45,48 mm (1½", female)
- 33,25 mm (1", male) - Ø 33 mm - Ø 25 mm

Approval marks:

