

Supplier	Article description	Art. No. / GTIN	Warranty	
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Booster Set HWG G-1000 Plus	30187	24 Months	
		4011458301874		
	Master Box Information			
	Master Box dimensions in cm			weight (kg) gross
	Width	Depth	Height	pack. Unit (pcs.)
-	-	-	-	
Article Information				
Color Box dimensions in cm			weight (kg) net / gross	
Width	Depth	Height	Qty.	
51,0	33,00	53,20	13,9 / 14,7	

Booster Set HWG G-1000 Plus	quantity / pallet:	
	quantity / truck:	

Description:
 Due to its robustness and its persuasive performance data the HWG G-1000 Plus is the perfect device for many applications. The heavy cast iron pump housing makes the HWG G-1000 Plus working very silent. Equipped with a high quality EPDM-membrane and a pressure gauge. Coming along with a big 22 l tank. Maintenance-free capacitor motor with thermal overload protection. The Hydraulic unit is Noryl. The Area of applications are: automatic domestic water supply from wells and cisterns, garden and automatic irrigation.

Technical Data:

Nominal performance:	800 Watt
Delivery height / pressure max.:	46 m / 4,6 bar
Flow rate max.:	58 l/min / 3,500 l/h
Suction height max.:	9 m
Pump housing:	Cast iron
Pressure tank / Volume:	Steel / 22 l
Pressure port:	30,93 mm (1", female)
Suction port:	30,93 mm (1", female)
Fluid temp. max.:	35 °C
Power cord:	1.5 m / H05RN-F
Number of sprinklers max.:	3



Approval marks:

