

( (





## **Model Number**

## OBG5000-R100-EP-IO-V3

Retroreflective sensor (glass) with 3-pin, M8 x 1 connector

## **Features**

- Miniature design with versatile mounting options
- Detects transparent objects, i.e., clear glass, PET and transparent films
- Two machines in one: clear object detection or reflection operating mode with long range
- High degree of protection IP69K
- IO-link interface for service and process data

# **Product information**


The R100 series miniature optical sensors are the first devices of their kind to offer an end-to-end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

# **Dimensions**



# **Electrical connection**




## **Pinout**

Wire colors in accordance with EN 60947-5-2



BN (brow BU (blue BK (blace

# Indicators/operating means



	0
	$\bigcirc$
L/D	N

1	Teach-in button		
2	Mode rotary switch		
3	Operating indicator / dark on		
4 Signal indicator			
5	Operating indicator / light on		

N	Normal mode			
I 10 % contrast detection				
Ш	18 % contrast detection			
III	40 % contrast detection			
L/D	Switching type			
0	Keylock			

Technical data		
General specifications		
Effective detection range		0 3.5 m in TEACH mode; 0 5 m at switch position "N"
Reflector distance		0 3.5 m in TEACH mode; 0 5 m at switch position "N"
Threshold detection range		6 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated visible red light
LED risk group labelling		exempt group
Diameter of the light spot		approx. 170 mm at a distance of 3.5 m
Angle of divergence		approx. 5 °
Ambient light limit		EN 60947-5-2
Functional safety related parame	ters	
MTTF <sub>d</sub>		600 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		. ==
Operation indicator		LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode
Function indicator		Yellow LED: Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve
Control elements		Teach-In key
Control elements		5-step rotary switch for operating modes selection
Contrast detection levels		10 % - clean, water filled PET bottles 18 % - clear glass bottles 40 % - colored glass or opaque materials Adjustable via rotary switch
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC
Ripple		max. 10 %
No-load supply current Protection class	I <sub>0</sub>	< 25 mA at 24 V supply voltage
Interface		III
Interface type		IO-Link ( via C/Q = pin 4 )
Transfer rate		COM 2 (38.4 kBaud)
IO-Link Revision		1.1
Min. cycle time		2.3 ms
Process data witdh		Process data input 2 Bit Process data output 2 Bit
SIO mode support		yes
Device ID		0x110A01 (1116673)
Compatible master port type		A
Output		The south-bigger and of the second is additionable. The defenda
Switching type		The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected, overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA , resistive load
Usage category		DC-12 and DC-13
Voltage drop	U <sub>d</sub>	≤ 1.5 V DC
Switching frequency	f	500 Hz
Response time		1 ms
Conformity		
Communication interface		IEC 61131-9
Product standard		EN 60947-5-2
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		44.5 mm
Housing depth		21.5 mm
Degree of protection		IP67 / IP69 / IP69K
Connection		M8 x 1 connector, 3-pin
Material		PO (P. I )
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 10 g

# **Accessories**

## REF-H85-2

Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

## REF-H50

Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap

# REF-H33

Reflector with screw fixing

## IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

## OFR-100/100

Reflective tape 100 mm x 100 mm

## OMH-R10X-01

Mounting bracket

#### OMH-R10X-02

Mounting bracket

### OMH-R10X-04

Mounting bracket

#### OMH-R10X-10

Mounting bracket

#### OMH-ML100-03

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

#### OMH-ML100-031

Mounting aid for round steel ø 10 ... 14 mm or sheet 1 mm ... 5 mm

REF-H32G-2

#### REF-ORR50G-2

## V31-GM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

# V31-WM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com


**FPEPPERL+FUCHS** 

Date of issue: 2019-03-26 267075-100040\_eng.xml


UL approval

E87056, cULus Listed, class 2 power supply, type rating 1

# **Curves/Diagrams**



#### Relative received light strength in switch position "N"



# **Settings**

# Teach-in:

267075-100040\_eng.xml

issue: 2019-03-26

Date of

date: 2019-03-26 09:34

Release

Use the rotary switch to select the required operating mode: Normal mode (N) or contrast level I - III.

To teach in a threshold or activate an operating mode, press the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s).

Release the "TI" button. Teach-in starts.

Successful teach-in is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs. The sensor will now operate in the selected operating mode with the taught-in threshold.

An unsuccessful teach-in is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs. After an unsuccessful teach-in, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Every taught-in switching threshold can be re-taught (overwritten) by pressing the "TI" button again.

Note: To ensure that the device functions reliably in Contrast mode, the device must be powered on at least 30 s before Teach-in.

Setting the Device to Maximum Sensitivity

Use the rotary switch to select the Normal mode (N) position.

Press the "TI" button for > 4 s. The yellow and green LEDs will go out.

Release the "TI" button.

The settings will be reset to maximum sensitivity. After successfully resetting, the yellow and green LEDs will flash alternately (2.5 Hz).

Switching between light on/dark on

Use the rotary switch to select the light on/dark on (L/D) position.

Press the "TI" button for > 1 s.

The respective operating indicator LED (L/D) will illuminate green and the switching type will change.

To reset the switching type, press the "TI" button for > 4 s.

The respective operating indicator LED (L/D) will illuminate green and the operating indicator will be reset to the most recently active switching type.

# **Reset to Default Settings**

Use the rotary switch to select the O position.

Press the "TI" button for > 10 s. The yellow and the green LEDs will both switch off.

Release the "TI" button. The yellow LED is on.

After resetting, the sensor will operate with the following default settings:

- Normal mode (N)
- Maximum sensitivity adjustment
- Dark on
- Pin 2 (white core): antivalent switching output

4