### Laser retroreflective sensor



#### **Model Number**

## OBR12M-R103-2EP-IO-V31-L

Laser retroreflective sensor with 4-pin, M8 x 1 connector

#### **Features**

- Miniature design with versatile • mounting options
- DuraBeam Laser Sensors durable ٠ and employable like an LED
- Extended temperature range • -40°C ... 60°C
- High degree of protection IP69K
- IO-link interface for service and process data


### **Product information**

The R103 series miniature optical sensors are the first devices of their kind to offer an end-to-end solution in a small single standard design - from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.




### **Electrical connection**




**Dimensions** 

#### Pinout



## Indicators/operating means



Ì		1
	Receiver	2
	Emitter	4
	J	

1	Light-on/dark-on changeover switch
2	Sensivity adjuster
3	Operating indicator / dark on
4	Function indicator
5	Operating indicator / light on

eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

Pepperl+Fuchs Group www.pepperl-fuchs.com fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Laserlabel

#### **Technical data**

General specifications Effective detection range Reflector distance Threshold detection range Reference target Light source Light type Polarization filter Laser nominal ratings Note Laser class Wave length Beam divergence Pulse length Repetition rate max. pulse energy Diameter of the light spot Angle of divergence Ambient light limit Functional safety related parameters MTTF<sub>d</sub> Mission Time (T<sub>M</sub>) Diagnostic Coverage (DC) Indicators/operating means Operation indicator

Control elements Control elements Parameterization indicator Electrical specifications Operating voltage Ripple No-load supply current Protection class Interface Interface type Transfer rate **IO-Link Revision** Min. cycle time Process data witdh SIO mode support Device ID Compatible master port type Output Switching type

Function indicator

Signal output

Switching voltage

Switching current Usage category Voltage drop Switching frequency Response time Conformity Communication interface Product standard Laser safety Ambient conditions Ambient temperature

Storage temperature

Housing height

**Mechanical specifications** Housing width

# yes LASER LIGHT, DO NOT STARE INTO BEAM

680 nm > 5 mrad d63 < 2 mm in the range of 250 mm ... 750 mm 1.6 µs max 176 kHz 9.6 nJ approx. 30 mm at a distance of 12 m approx. 0.3 EN 60947-5-2

#### 672 a 20 a 0%

UB

 $I_0$ 

0 ... 12 m 0.25 ... 12 m

H50 reflector

modulated visible red light

laser diode

15 m

LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Yellow LED Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve Light-on/dark-on changeover switch sensitivity adjustment IO link communication: green LED goes out briefly (1 Hz)

10 ... 30 V DC max 10 % < 20 mA at 24 V supply voltage ш

IO-Link (via C/Q = pin 4) COM 2 (38.4 kBaud) 1.1 2.3 ms Process data input 2 Bit Process data output 2 Bit ves 0x110205 (1114629)

Α

Ud

f

### The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - Pin2: NPN normally closed / light-on, PNP normally open / dark-on 2 push-pull (4 in 1)outputs, short-circuit protected, reverse polarity protected, overvoltage protected max. 30 V DC max. 100 mA , resistive load DC-12 and DC-13 $\leq$ 1.5 V DC 2000 Hz 250 µs IEC 61131-9 EN 60947-5-2 EN 60825-1:2014 -40 ... 60 °C (-40 ... 140 °F) -40 ... 70 °C (-40 ... 158 °F)



Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

## Accessories

#### IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

## OMH-R103-01

Mounting bracket

V31-GM-2M-PUR Female cordset, M8, 4-pin, PUR cable

V31-WM-2M-PUR Female cordset, M8, 4-pin, PUR cable

### REF-MH82

Reflector with Micro-structure, rectangular 82 mm x 60 mm, mounting holes

### REF-MH50

Reflector with Micro-structure, rectangular 50.9 mm x 50.9 mm, mounting holes, fixing strap

### REF-MH20

Reflector with Micro-structure, rectangular 32 mm x 20 mm, mounting holes

### REF-MVR10

Reflector with Micro-structure, rectangular 60 mm x 19 mm, mounting holes

OMH-R101-Front Mounting Clamp

**OMH-R101** Mounting Clamp

**OMH-4.1** Mounting Clamp

OMH-ML6

Mounting bracket

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

15 mm

43.9 mm

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



267075-100298\_eng.xml

Date of issue: 2018-09-19

Release date: 2018-06-08 14:14


## Laser retroreflective sensor


Housing depth	26.7 mm
Degree of protection	IP67 / IP69 / IP69K
Connection	M8 x 1 connector, 4-pin
Material	
Housing	PC (Polycarbonate)
Optical face	РММА
Mass	approx. 12 g
Approvals and certificates	
UL approval	E87056 , cULus Listed , class 2 power supply , type rating 1

FDA approval

IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

## **Curves/Diagrams**







- 2 Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range adjuster / sensitivity adjuster for more than 180 degrees.

## Sensing Range/ Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

eng.xm	
67075-100298	
e of issue: 2018-09-19 2	
ate: 2018-06-08 14:14 Dat	
Release d	

R103

5 4 3

-



If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

#### Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on /dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

#### **Restore Factory Settings**

Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.



4