





Dimensions



Model Number

SB4 Module 6C


Safety control unit module

Module for Evaluation unit SafeBox - series SB4

Features

- Sensor module
- 6 sensor channels
- Single module for safety thru-beam sensors SLA12 and SLA29 and for 2 channel safety devices (emergency off)
- Operating mode can be selected by means of DIP switches

Electrical connection



Terminal	Function
1	Transmitter 1 output
2	Transmitter 2 output
3	Transmitter 3 output
4	Transmitter 1...3 +U
5	Transmitter 4 output
6	Transmitter 5 output
7	Transmitter 6 output
8	Transmitter 4...6 +U
9	Receiver 1 input
10	Receiver 2 input
11	Receiver 3 input
12	Receiver 1...3 +U
13	Receiver 4 input
14	Receiver 5 input
15	Receiver 6 input
16	Receiver 4...6 +U

Technical data

General specifications

Operating mode simultaneousness, antivalence

Functional safety related parameters

Safety Integrity Level (SIL) SIL 3
 Performance level (PL) PL e
 Category Cat. 4
 Mission Time (T_M) 20 a
 Type 4

Indicators/operating means

Function indicator LED yellow (6x): indicator lamp channel 1 ... 6
 Pre-fault indicator LED yellow flashing: Indicator lamp channel 1 ... 6
 Control elements DIP-switch

Electrical specifications

Operating voltage U_B 24 V DC ± 20 % , via SB4 Housing

Input

Activation current approx. 7 mA

Conformity

Functional safety ISO 13849-1 ; EN 61508 part1-4
 Product standard EN 61496-1

Ambient conditions

Ambient temperature 0 ... 50 °C (32 ... 122 °F)
 Storage temperature -20 ... 70 °C (-4 ... 158 °F)

Mechanical specifications

Degree of protection IP20
 Connection screw terminals , lead cross section 0.2 ... 2 mm²
 Material

Release date: 2017-12-05 15:18 Date of issue: 2017-12-05 182111_eng.xml

Housing	Polyamide (PA)
Mass	approx. 150 g
Approvals and certificates	
CE conformity	CE
UL approval	cULus
TÜV approval	TÜV

The operation of this module is possible only within a control unit of the type SafeBox SB4.

The operating instruction of the SafeBox has to be observed.

Function

The 6-channel sensor card module SB4-6C makes it possible to connect light barriers or light grids or contact safety sensors in a one or two-channel version.

When the system is switched on, the software determines whether a light barrier or a contact safety sensor is switched on at a channel and monitors its presence during operation. Safety sensors with switching contacts, which are connected to the SafeBox, must operate in the switching mode "normally closed". An open contact means "safe status".


The channels 1 and 2, 3 and 4 as well as 5 and 6 can be monitored for simultaneousness or antivalence. If simultaneousness monitoring is activated, 2 channel safety equipment is monitored for simultaneous opening or changing of the signals. The monitoring time is 2 s.

Antivalence monitoring expects the normally closed contact at channel 1, 3 or 5 and the normally open contact at channel 2, 4 or 6. If antivalence monitoring is performed without simultaneousness monitoring, an incorrect contact position causes a switch-off and the error message 7 after approx. 60 s .

Operation types

The assembly contains 4 DIP switches for selecting the simultaneousness functions of neighbouring channels (1 and 2, 3 and 4, 5 and 6) and for an antivalent evaluation of neighbouring channels (1 and 2, 3 and 4, 5 and 6). For selecting functions, 2 selector switches must always be actuated. The functions are not effective if light barriers are connected.

Position of the DIP switches



Switch	Position	Operation type
1 and 3	OFF	No antivalent evaluation
	ON	Antivalent evaluation active
2 and 4	OFF	No simultaneousness evaluation
	ON	Simultaneousness evaluation active

Display

For each channel, there is a yellow LED on the front panel of the module.

Display	LED	Meaning
R1 - R6	yellow	Status of light barrier 1 ... 6 Off: light beam interrupted On: light beam released Flashing (2.5 Hz): light beam released, function reserve fallen short of Flashing (5 Hz): error

Release date: 2017-12-05 15:18 Date of issue: 2017-12-05 182111_eng.xml