





(€





Model Number


RL31-54/115b/136

Retroreflective sensor with 0.3 m fixed cable and M12 connector, 4-pin


Features

- · Compact and stable housing
- · Glare protected with polarization filter
- Highly visible LED
- Powerful push-pull output
- Protection class II

Dimensions



Electrical connection




- O = Light on
- = Dark on

Pinout



Indicators/operating means



1	1 Operating display g		
2 Signal display yello			
3	Emitter		
4	Receiver		

Technical data					
General specifications					
Effective detection range		0 9000 mm			
Reflector distance		20 9000 mm			
Threshold detection range		12 m			
Reference target		reflector C110-2			
Light source		LED			
Light type		modulated visible red light, 630 nm			
Polarization filter		yes			
Diameter of the light spot		approx. 200 mm at a distance of 6 m			
Angle of divergence		3°			
Ambient light limit		50000 Lux ; according EN 60947-5-2			
Functional safety related parameters					
MTTF _d		920 a			
Mission Time (T _M)		20 a			
Diagnostic Coverage (DC)		0 %			
Indicators/operating means					
Operation indicator		LED green: power on			
Function indicator		LED yellow:			
		LED lit constantly: signal > 2 x switching point (function reserve)			
		2. LED flashes: signal between 1 x switching point and 2 x swit-			
		ching point			
		3. LED off: signal < switching point			
Electrical specifications					
Operating voltage	U_B	10 30 V DC			
Ripple		10 %			
No-load supply current	I ₀	≤ 20 mA			
Output					
Switching type		dark on			
Signal output		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected			
Switching voltage		max. 30 V DC			
Switching current		max. 100 mA			
Voltage drop	U_d	≤ 1.5 V			
Switching frequency f		≤ 500 Hz			
Response time		≤1 ms			
Ambient conditions					
Ambient temperature		-30 55 °C (-22 131 °F)			
Storage temperature		-40 70 °C (-40 158 °F)			
Mechanical specifications					
Degree of protection		IP67			
Connection		300 mm fixed cable with M12 x 1, 4-pin connector			
Material					
Housing		plastic			
Optical face		PMMA			
Mass		133 g			
Compliance with standards and directives					
Directive conformity		EMC Directive 2004/108/EC			
Standard conformity					
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007			
Approvale and contification					
Approvals and certificates Protection class II . rated insulation voltage < 250 V AC with pollution degree					
Protection class		II , rated insulation voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN 50178, rated insulation voltage 240 V AC			
UL approval		cULus Listed, Class 2 Power Source, Type 1 enclosure			
CCC approval		CCC approval / marking not required for products rated ≤36 V			

Accessories

OMH-RL31-01

Mounting bracket

OMH-RL31-02

Mounting bracket narrow

OMH-RL31-03

Mounting bracket narrow

OMH-RL31-04

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

OMH-RL31-05

Mounting bracket with M10 threaded rod

OMH-RL31-06

Stainless steel mounting bracket with adjustable half clamp on the side

Other suitable accessories can be found at www.pepperl-fuchs.com

Curves/Diagrams

