



 $\epsilon$ 



## **Model Number**

#### ML100-8-1000-RT/98/102

Diffuse mode sensor with 3-pin, M8 x 1 connector


### **Features**

- Miniature design
- Easy to use
- Very bright, highly visible light spot
- · Full metal thread mounting
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light


# **Product information**

The ML100 series is characterized by its miniature housing with integral, all-metal threaded bushings. All versions are equipped with a visible red transmitter LED. This greatly simplifies installation and commissioning. The switching states are easily visible from all directions thanks to the highly visible LEDs.

### **Dimensions**



## **Electrical connection**



- O = Light on
- = Dark on


## **Pinout**

Wire colors in accordance with EN 60947-5-2

3 (C)

1 BN (brown) 3 BU (blue) 4 BK (black)

## Indicators/operating means



1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display	yellow
4	Operating display	green

#### **Technical data** General specifications 0 ... 1000 mm Detection range Adjustment range 100 ... 1000 mm standard white, 100 mm x 100 mm Reference target Light source modulated visible red light Light type Polarization filter approx. 75 mm at a distance of 1000 mm Diameter of the light spot Angle of divergence approx. 2 ° Optical face frontal EN 60947-5-2:2007+A1:2012 Ambient light limit Functional safety related parameters 860 a $MTTF_d$ Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator LED yellow, lights up with receiver lit Control elements sensitivity adjustment Control elements Light-on/dark-on changeover switch **Electrical specifications** 10 ... 30 V DC Operating voltage max. 10 % Ripple No-load supply current < 20 mA Output Switching type The switching type of the sensor is adjustable. The default setting is: light on Signal output 1 NPN output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load ≤ 1.5 V DC Voltage drop Switching frequency 1000 Hz 0.5 ms Response time **Ambient conditions** -30 ... 60 °C (-22 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Degree of protection

Male connector M8 x 1, 3-pin

PC (Polycarbonate)

EN 60947-5-2

UL 60947-5-2

PMMA approx. 10 g

#### **Accessories**

#### OMH-ML100-03

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

#### OMH-ML100-04

Mounting aid for ML100 series, Mounting bracket

### OMH-ML100-05

Mounting aid for ML100 series, Mounting bracket

#### OMH-F10-ML100

Mounting aid for ML100 series

#### **OMH-10**

Mounting aid

#### V3-WM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

#### OMH-ML100-08

Mounting aid for ML100 series, Snap-in

Other suitable accessories can be found at www.pepperl-fuchs.com

cULus Listed, Class 2 Power Source or listed Power Supply

CCC approval / marking not required for products rated ≤36 V

with a limited voltage output with (maybe integrated) fuse

(max. 3.3 A according UL248), Type 1 enclosure

Connection

Optical face

Directive conformity

Standard conformity

Standards

**UL** approval

CCC approval

Compliance with standards and directi-

EMC Directive 2004/108/EC

Approvals and certificates

Material Housing

Mass

# **Curves/Diagrams**

