











# VISC+

## **Model Number**


# VT18-8-400-M-LAS/32/40a/118


Diffuse mode sensor with 4-pin, M12 x 1 connector

## **Features**


- M18 threaded housing made of brass, nickel plated
- Visible red light, pulsed LASER light
- Array control panel with highly visible LED display
- Flashing power on LED in case of short-circuit
- Multiple device installation possible, no mutual interference (no cross-talk)
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II

## **Dimensions**





## **Electrical connection**



- O = Light on
- = Dark on

## **Pinout**

1 4

Wire colors in accordance with EN 60947-5-2

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

#### **Technical data General specifications** 0 ... 400 mm, adjustable Detection range 0 ... 25 mm Detection range min. 0 ... 400 mm Detection range max. Light source laser diode modulated visible red light Light type Laser nominal ratings LASER LIGHT, DO NOT STARE INTO BEAM Note Laser class Wave length 655 nm Beam divergence 31.5 mrad Pulse length $4 \, \mu s$ 11.91 kHz Repetition rate max. pulse energy 4.95 nJ Diameter of the light spot approx. 0.5 mm at a distance of 120 mm Optical face frontal Ambient light limit 30000 Lux Hysteresis < 15 % Н Functional safety related parameters $MTTF_d$ 700 a Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green, flashes in case of short-circuit Function indicator LED yellow, lights up with receiver lit Control elements Sensing range adjuster, light-on/dark-on changeover switch **Electrical specifications** Operating voltage $U_{\mathsf{B}}$ 10 ... 30 V DC, class 2 No-load supply current < 25 mA $I_0$ Protection class II, rated voltage ≤ 50 V AC with pollution degree 1-2 according to IEC 60664-1 Output Switching type light/dark on, switchable Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector 30 V DC Switching voltage Switching current max. 200 mA Switching frequency 500 Hz Response time 1 ms **Ambient conditions** Ambient temperature -25 ... 55 °C (-13 ... 131 °F) -30 ... 70 °C (-22 ... 158 °F) Storage temperature **Mechanical specifications** Degree of protection IP67 Connection 4-pin, M12 x 1 connector Material Housing brass, nickel-plated Optical face **PMMA** Mass 60 g Compliance with standards and directives EMC Directive 2004/108/EC Directive conformity Standard conformity Product standard EN 60947-5-2:2007 IEC 60947-5-2:2007 Laser class IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007 Approvals and certificates CE conformity yes UL approval cULus Listed. Type 1 enclosure CCC approval CCC approval / marking not required for products rated ≤36 V

## **Accessories**

#### OMH-VL18

Mounting Bracket with swivel nut

#### **BF 18**

Mounting flange, 18 mm

### **BF 18-F**

Plastic mounting adapter, 18 mm

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

### V1-G-2M-PUR

Female cordset, M12, 4-pin, PUR cable


#### V1-W-2M-PUR


Female cordset, M12, 4-pin, PUR cable


Other suitable accessories can be found at www.pepperl-fuchs.com

PEPPERL+FUCHS


# **Curves/Diagrams**







## **Curves/Diagrams**




## **Adjustment**

## Sensitivity adjustment

- Turn sensitivity adjuster (counterclockwise) to minimum position.
- Place the object to be detected in the sensing range and turn the sensitivity adjuster clockwise until the yellow indication LED lights up. This setting indicates the position A of the sensitivity adjuster.
- · Remove the object. Increase the sensitivity slowly (turning the sensitivity adjuster clockwise) until the yellow LED lights up again. This setting indicates the position B of the sensitivity adjuster.



In case of no background object, the LED won't light up, even in MAX. adjustment. In that case take care, that in normal operation conditions no temporal background object can appear in the sensing range (e. g. parked pallets). If this can not be excluded, place (only for adjustment matter) an object at the appropriate location. Then repeat this adjustment step. After finishing the adjustment this temporal object should be



· For optimal setting, now turn the sensitivity adjuster to the middle position between the positions A and B.

# Laser notice laser class 1

- The irradiation can lead to irritation especially in a dark environment. Do not point at people!
- Maintenance and repairs should only be carried out by authorized service personnel!
- Attach the device so that the warning is clearly visible and readable.
- The warning accompanies the device and should be attached in immediate proximity to the device.
- Caution Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

PEPPERL+FUCHS