Dimensions



CE **OIO**-Link

Model Number

MLV41-8-H-500-RT-IO/65b/95/136


Background suppression sensor with 4-pin, M8 x 1 connector

Features


- Rugged series in corrosion-resistant • metal housing
- MPT Multi Pixel Technology ٠
- IO-link interface for service and pro-• cess data
- Reliable detection of all surfaces, in-• dependent of color and structure
- Precision background suppression, • adjustable
- Low sensitivity to target color
- Clear and functional display concept • for the operating modes

Product information

The diffuse mode sensor with MPT technology combines the benefits of the triangulation principle with the measuring functionality of a distance sensor. The integrated measuring principle provides an extremely wide range of switching element functions in one device, along with a large detection range and a small black/white difference up to the final detection range. The sensor is equipped with an IO-Link interface, through which the measuring principle is optimized to the requirements of the relevant application.



Electrical connection






Pinout



Indicators/operating means



Pepperl+Fuchs Group

fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com



Technical data			
General specifications			
Detection range		20 500 mm Black-white difference < 5%	
Adjustment range		40 500 mm	
Diagnosis range		20 500 mm	
Reference target		standard white, 100 mm x 100	
Light source		LED	
Light type		modulated visible red light	
Diameter of the light spot	Diameter of the light spot		
Angle of divergence		approx. 3 °	
Ambient light limit		25000 Lux	
unctional safety related param	neters		
MTTF _d		500 a	
Mission Time (T _M)		20 a	
Diagnostic Coverage (DC)		0 %	
ndicators/operating means			
Operation indicator		LED green, statically lit Power Green LED, pulsing (approx. (flashing (approx. 4 Hz)	
		2 LEDs yellow ON: object inside the scannin OFF: object outside the scann	
Control elements Parameterization indicator		Detection range adjuster	
		IO link communication: green	
Electrical specifications			
Operating voltage	UB	10 30 V DC , class 2 max. 10 %	
Ripple No-load supply current	I ₀	max. 10 % max. 25 mA at 24 V supply vo	
nterface	10	max. 25 mA at 24 V supply Vo	
Interface type		IO-Link	
Protocol		IO-Link V1.0	
Mode		COM 2 (38.4 kBaud)	
Dutput			
Switching type		dark on	
Signal output		2 push-pull (4 in 1) outputs, sh rity protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	Ud	\leq 2 V DC	
Switching frequency	f	200 Hz	
Response time		2.5 ms	
mbient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-40 75 °C (-40 167 °F)	
lechanical specifications			
Degree of protection		IP67	
Connection		M8 x 1 connector, 4-pin	
Material			
Housing		aluminum , Delta-Seal coated	
Optical face		glass pane	
Connector		metal	
Mass Compliance with standards and	d direct	approx. 40 g i-	
es Diversitive sectoresite			
Directive conformity EMC Directive 2004/108/EC		EN 60947-5-2:2007	
Standard conformity		LIN 00077-0-2.2007	
Product standard		EN 60947-5-2:2007	
- roude standard		IEC 60947-5-2:2007	
Approvals and certificates			
UL approval		cULus Listed 57M3 (Only in a supply; Type 1 enclosure)	
000			

ifference < 5% e, 100 mm x 100 mm sible red light m at sensor range 500 mm atically lit Power on , Undervoltage indicator: ulsing (approx. 0.8 Hz) , short-circuit : LED green ox. 4 Hz) side the scanning range utside the scanning range ge adjuster unication: green LED goes out briefly (1 Hz) , class 2 t 24 V supply voltage kBaud) in 1) outputs, short-circuit protected, reverse pola-

Accessories

OMH-09 Mounting bracket for Sensors series MLV41 for M12 rod mounting

OMH-40 Mounting bracket

OMH-41 Mounting bracket

V31-WM-2M-PUR Female cordset, M8, 4-pin, PUR cable

V31-GM-2M-PUR Female cordset, M8, 4-pin, PUR cable

IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

IODD Interpreter DTM

Software for the integration of IODDs in a frame application (e.g. PACTware)

MLV41-8 IODD

IODD for communication with MLV41-8-**IO-Link sensors**

Other suitable accessories can be found at www.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

57M3 (Only in association with UL Class 2 power


CCC approval / marking not required for products rated ${\leq}36~V$



2

CCC approval

Curves/Diagrams



Setting information

Detection range adjustment:

The detection range can be adjusted between 40 mm and 500 mm via the rotary switch or IO-Link. For finer adjustment, the adjustable detection range is divided into several subranges which can be selected using Page Up/Down.

The value set with IO-Link is always assigned the current rotary switch configuration.

Setting using the rotary switch:

Increasing the detection range:

Turn the potentiometer to the right. If the desired detection range is not reached, turn the potentiometer to the right until it stops (Page Up). The green LED will flash briefly. Now set the desired detection range again.

Reducing the detection range:

Turn the potentiometer to the left. If the desired detection range is not reached, turn the potentiometer to the left until it stops (Page Down). The green LED will flash briefly. Now set the desired detection range again.

Example application: manually reduce detection range from 450 mm to 60 mm:



The potentiometer has a position as shown here, but works with a 450 mm detection range.



Now turn the potentiometer completely to the left until it stops (Page Down). The green LED will flash briefly.



Now set the detection range to 60 mm. If the desired detection range cannot be set, turn the potentiometer again to the left until it stops (Page Down) and repeat the procedure.

Background

suppression

Setting via IO-Link interface

Setting different operating modes via IO-Link interface

The devices have an IO-Link interface as standard for diagnostic and parameterization tasks enabling optimum adaptation of the sensors to the application. In addition, four different operating modes can be set:

Background suppression operating mode (1 or 2 switching points):

- Detection of objects irrespective of type and color in a defined sensing range. Objects in the background are reliably suppressed
- · Background suppression with 2 switching points

active detection range

Background evaluation operating mode:

Detection of objects irrespective of type and color against a defined background. Reliable detection of objects at close range (detection range >= 0 mm). The background serves as reference



activo	detection range	
active	uciccilon range	

V

Background evaluation

Window operation operating mode:

Output

• Detection of objects irrespective of type and color in a defined sensing range. Reliable detection when leaving the defined sensing range.

a	active detection range	
Foreground suppression	В	ackground suppression
Hysteresis operating mode:Detection of objects irrespective of type	be and color between a defined s	witch-on and switch-off point
	active detection range	I
		Uutput

Hysteresis

To use the diagnostic and parameterization options, you will find the compatible IODD, and if required, the FDT base application PACTware in the download area at www.pepperl-fuchs.com.

4

