



((





Model Number

RL28-8-H-2000-IR/47/105/106

Background suppression sensor with 5-pin, M12 x 1 plastic connector


Features

- Universal series with highly versatile fields of use
- Resistant against noise: reliable operation under all conditions
- Minimal black-white difference through the infrared transmission LED
- · Version with heated front panel


Product information

The series 28 family of sensors can be universally used. It has a large range of models that allows it to be integrated into any automation environment. The sensors are contained in sturdy water resistant plastic housings with multiple fastening options and scratch resistant optical cover. Features such as a timer function, and functions including a light/dark switch, sensitivity adjuster and highly visible status LEDs make for less effort on the part of the user and streamline installation, setup and operation. Just about any task associated with positioning, moving, conveying and monitoring can be accomplished with these sensors.

Dimensions



Electrical connection



O = Light on

= Dark on


Pinout

Wire colors in accordance with EN 60947-5-2



1 | BN (brown)
2 | WH (white)
3 | BU (blue)
4 | BK (black)
5 | GY (gray)

Indicators/operating means



1	Operating display green
2	Switch state yellow
3	Bright/dark switch
4	Detection range adjuster
5	Receiver
6	Emitter

www.pepperl-fuchs.com

Technical data General specifications 20 ... 2000 mm Detection range Detection range min. 20 ... 200 mm Detection range max. 20 ... 2000 mm Background suppression max. + 10 % of the upper limit of the detection range **IRED** Light source Light type modulated infrared light, 880 nm Black/White difference (6 %/90 %) < 40 % Diameter of the light spot approx. 70 mm at a distance of 2000 mm Angle of divergence transmitter 2° receiver 2° 50000 Lux Ambient light limit Functional safety related parameters 720 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means LED green Operation indicator Function indicator 2 LEDs yellow ON: object inside the scanning range OFF: object outside the scanning range Control elements Sensing range adjuster, Light-on/dark-on changeover switch **Electrical specifications** Operating voltage U_{B} 24 V DC \pm 20 % Ripple 10 % No-load supply current I_0 ≤ 75 mA Output Switching type light/dark on switchable Signal output 2 PNP, complementary, short-circuit protected, reverse polarity protected , open collectors Switching voltage max. 30 V DC Switching current max. 200 mA Switching frequency 250 Hz f Response time Conformity EN 60947-5-2 Product standard **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Storage temperature -40 ... 75 °C (-40 ... 167 °F) **Mechanical specifications** Housing width 25.8 mm Housing height 88 mm Housing depth 54.3 mm Degree of protection IP67 Connection 5-pin, M12 x 1 connector Material Plastic ABS Housing Optical face Plastic pane Mass 70 g Heated lens Note Approvals and certificates II, rated voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1 Protection class

Accessories

OMH-05

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

OMH-21

Mounting bracket

OMH-22

Mounting bracket

OMH-MLV11-K

dove tail mounting clamp

OMH-RLK29-HW

Mounting bracket for rear wall mounting

OMH-RL28-C

Weld slag cover model


Other suitable accessories can be found at www.pepperl-fuchs.com

PEPPERL+FUCHS

UL approval

E87056, cULus Listed, class 2 power supply, type rating 1

Characteristic response curve Offset Y [mm] 15 10 5 -10 -15 500 1000 1500 2000 Distance X [mm] white 90 % grey 18 % black 6 %



Additional information

Intended use:

The transmitter and receiver are located in the same housing for direct detection sensors with background masking. Marking of objects outside the detection range is achieved by arranging the angle between the transmitter and receiver (2 receiver elements).

Objects are detected independently of their surface structures, brightness and colour, as well as the brightness of the background.

Mounting instructions:

The sensors can be fastened directly with fixing screws or with a support bracket (not included with delivery).

The surface underneath must be flat to prevent the housing from moving when it is tightened into position. We recommend securing the nut and screw in place with spring washers to prevent the sensor from going out of adjustment.

Adjustment:

183415_eng.xml

Date of issue: 2018-03-26

Release date: 2018-03-26 09:53

After the operating voltage is applied, the LED is lit green.

Align the sensor to the background. If the yellow LED is lit, the detection range should be reduced with the detection range adjuster until the yellow LED goes out.

Object direction:

Place the object to be detected at the desired maximum detection range and align the light spot to it. If the object is detected, the yellow LED lights up.

If it does not light up, the detection range must be adjusted on the potentiometer until it lights up when an object is detected.

Cleaning:

We recommend cleaning the optical surface and checking the screwed connection and other connections at regular intervals.