31



CE

Model Number

ML100-55/95/102

Retroreflective sensor with 4-pin, M8 x 1 connector


Features

- Miniature design •
- Easy to use •
- Very bright, highly visible light spot •
- Full metal thread mounting •
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Not sensitive to ambient light ٠


Product information

The ML100 series is characterized by its miniature housing with integral, all-metal threaded bushings. All versions are equipped with a visible red transmitter LED. This greatly simplifies installation and commissioning. The switching states are easily visible from all directions thanks to the highly visible LEDs.

Dimensions



Electrical connection




Pinout



Indicators/operating means

²₁ 3



1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display	yellow
4	Operating display	green

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



	Accessories
	OMH-F10-ML100 Mounting aid for ML100 series
	OMH-ML100-01 Mounting aid for ML100 series, Mounting bracket
	OMH-ML100-03 Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04 Mounting aid for ML100 series, Mounting bracket
	OMH-10 Mounting aid
am ; flashes en light beam is	REF-H85-2 Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
	REF-C110-2 Reflector, round ø 84 mm, central moun- ting hole
	REF-H60-2 Reflector with mounting holes
ne default set- arity protected,	REF-H50 Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap
	REF-H33 Reflector with screw fixing
	OFR-70-2 Reflective tape 70 mm x 70 mm
	REF-MH23-2 Reflector with Micro-structure, rectangu- lar 23 mm x 14 mm, diagonal mounting hole
	V31-WM-2M-PUR Female cordset, M8, 4-pin, PUR cable
	V31-GM-2M-PUR Female cordset, M8, 4-pin, PUR cable
	OMH-ML100-S1 Mounting bracket
	OMH-ML100-08 Mounting aid for ML100 series, Snap-in
ower Supply ted) fuse	Other suitable accessories can be found at www.pepperl-fuchs.com
e ts rated ≤36 V	-03- -03- -03-
	201 7 Tsue: 201 7
	Date of it
	-31 11:29
	: 2017-0 3 .
	Release date: 2017-03-31 11:29
	e E

Technical data General specifications Effective detection range 0...5m Reflector distance 0.01 ... 5 m Threshold detection range 7 m H50 reflector Reference target I FD Light source Light type Polarization filter yes Diameter of the light spot Angle of divergence approx. 4 ° Optical face frontal Ambient light limit Functional safety related parameters 860 a MTTF_d Mission Time (T_M) 20 a 0% Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: power on Function indicator interrupted Control elements Control elements **Electrical specifications** 10 ... 30 V DC Operating voltage U_B Ripple max. 10 % No-load supply current I₀ < 20 mA Output Switching type ting is: light on Signal output open collector Switching voltage max. 30 V DC Switching current < 1.5 V DC Voltage drop U_{d} 1000 Hz Switching frequency Response time 0.5 ms Ambient conditions Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Degree of protection IP67 Connection Material Housing Optical face **PMMA** Mass approx. 10 g Tightening torque, fastening screws 0.6 Nm Compliance with standards and directives Directive conformity EMC Directive 2004/108/EC Standard conformity Standards UL 60947-5-2 Approvals and certificates UL approval

CCC approval

modulated visible red light approx. 500 mm at a distance of 7 m EN 60947-5-2:2007+A1:2012

LED yellow: lights up when receiving the light bear when falling short of the stability control; OFF when sensitivity adjustment Light-on/dark-on changeover switch

The switching type of the sensor is adjustable. The

1 NPN output, short-circuit protected, reverse pola max. 100 mA , resistive load

-30 ... 60 °C (-22 ... 140 °F)

connector M8 x 1 , 4-pin

PC (Polycarbonate)

EN 60947-5-2:2007+A1:2012

cULus Listed, Class 2 Power Source or listed Pow with a limited voltage output with (maybe integrate (max. 3.3 A according UL248), Type 1 enclosure CCC approval / marking not required for products

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com





2

Pepperl+Fuchs Group www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Curves/Diagrams





Release date: 2017-03-31 11:29 Date of issue: 2017-03-31 210535_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001 www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

