Dimensions



CE **VISC**� C US

#### **Model Number**

#### ML6-54-G/25/95/136

Retroreflective sensor


with 4-pin, M8 x 1 connector

#### **Features**

- Precision sensor for standard applica-• tions
- Miniature design with very robust and ٠ versatile mounting options
- Reliable recognition of reflective ob-• jects and clear glass
- Two machines in one: clear object detection or reflection operating mode with long range
- TEACH-IN switch for setting the contrast detection levels
- Automatic adjustment in case of soiling in contrast detection mode
- Rear mounting option for easy mounting without mounting bracket


#### **Product information**

The ML6 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/IP69K degree of protection, a food-grade lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors with a double push-pull output are available. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges. Clearly visible red light sources facilitates alignment. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application fields.



## **Electrical connection**

Option:






Pinout

4



## Indicators/operating means



Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



## Technical data

Technical data			
General specifications			
Effective detection range		0 3.5 m in TEACH mode 0 5 m at switch position "N"	
Reflector distance		0 3.5 m in TEACH mode 0 5 m at switch position "N"	
Threshold detection range		6 m	
Reference target		H85-2 reflector	
Light source		LED	
Light type		modulated visible red light , 660 nm	
Angle deviation		max. ± 1°	
Diameter of the light spot		approx. 40 mm at detection range 1 m	
Angle of divergence		1.7 °	
Ambient light limit			
Continuous light		40000 Lux	
Modulated light		5000 Lux	
Functional safety related parame	ters		
MTTF <sub>d</sub>		980 a	
Mission Time (T <sub>M</sub> )		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means			
Operating display		LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)	
Function display		LED yellow: switching state ; Stability control ; Teach-In	
Controls		5-step switch for setting the contrast detection levels.	
Contrast detection levels		switch position I: 10 % - clean, water filled PET bottles switch position II: 18 % - clear glass bottles switch position III: 40 % - coloured glass or opaque materials adjustable due to TEACH-IN switch	
Electrical specifications			
Operating voltage	UB	10 30 V DC	
Ripple		max. 10 %	
No-load supply current	I <sub>0</sub>	< 15 mA at 24 V DC	
Output			
Switching type		light/dark on, programmable	
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	Ud	≤ 2.5 V DC	
Switching frequency	f	1 kHz	
Response time		500 μs	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-20 75 °C (-4 167 °F)	
Mechanical specifications			
Protection degree		IP67 / IP69K	
Connection		M8 x 1 connector, 4-pin	
Material			
Housing		ABS	
Optical face		PMMA	
Mass		approx. 10 g	
Compliance with standards and ves	directi-		
Standard conformity		EN 60047 5 0:0007	
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007	
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions	
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y and Z directions	
Approvals and certificates			
CE conformity		yes	
UL approval		cULus Listed	
CCC approval		CCC approval / marking not required for products rated $\leq$ 36 V	


ME0-34-G/23/93/130
Accessories
OMH-4.1
Mounting Clamp OMH-ML6
Mounting bracket
OMH-ML6-U Mounting bracket
OMH-ML6-Z Mounting bracket
OMH-11-02 Aperture-V-H 0.5 mm Slit diaphragm can be affixed for detec- ting very small parts
OMH-11-04 Aperture-V-H 1.0 mm Slit diaphragm can be affixed for detec- ting very small parts
OMH-11-06 Aperture-V-H 1.5 mm Slit diaphragm can be affixed for detec- ting very small parts
OMH-11-08 Aperture-V-H 2.0 mm Slit diaphragm can be affixed for detec- ting very small parts
V31-GM-2M-PVC M8, 4-pin socket, PVC cable
V31-WM-2M-PVC M8, 4-pin socket, PVC cable
<b>REF-H85-2</b> Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
<b>REF-C110-2</b> Reflector, round ø 84 mm, central moun- ting hole
REF-H60-2 Reflector with mounting holes
<b>REF-VR10</b> Reflector, rectangular 60 mm x 19 mm, mounting holes
<b>OFR-100/100</b> Reflective tape 100 mm x 100 mm
<b>REF-A17</b> Reflector, round ø 20.5 mm, self-adhesive
REF-A25 Reflector, round ø 25 mm, self-adhesive
Reflector, round ø 25 mm, self-adhesive <b>REF-MH23</b> Reflector with Micro-structure, rectangu- lar 23 mm x 13.8 mm, diagonal mounting hole <b>REF-CLIP50HT</b> Reflector, round ø 50 mm, snap-in, high temperature applications <b>REF-H50HT</b> Reflector, rectangular 50.9 mm x 50.9 mm, mounting holes, fixing strap Suitable reflectors and cable sockets can be found in the Internet
REF-CLIP50HT Reflector, round ø 50 mm, snap-in, high temperature applications
REF-H50HTاللهReflector, rectangular 50.9 mm x 50.9ه.mm, mounting holes, fixing strapه.
Suitable reflectors and cable sockets can be of found in the Internet
ease date:


2


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

## **Curves/Diagrams**







Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001


www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com





## **Additional information**

# Adjustment instructions for Teach-In operation:

Step	Switch	LED	LED	Time/	Explanations/
	position	green	yellow	frequency	comments
1	N	on	flashes	4/s	In switch position "N" directed towards reflector.
					Reflector detected without function reserve.
	N	on	on	-	In switch position "N" directed towards reflector.
					Reflector detected with function reserve (recommended).
2	Т	off/on	on	200 ms	The selection of a new switch position is indicated by the green LED going out for a short time.
					This also applies to the selection of the other switch positions.
	Т	flashes	flashes	2.5 s	<i>Slow</i> alternating flashing: Teach-In process has been performed <b>correctly</b> .
					Max. duration of the Teach-In process: 2 s
	Т	flashes	flashes	8/s	<i>Quick</i> alternating flashing: Teach-In process has <b>not</b> been performed <b>correctly</b> . (e.g. receiver signal not sufficient, sensor not directed correctly towards reflector).
					Status is terminated by turning switch to position N.
3/1	1	on	on	-	Contrast detection 10 % is activated. (e.g. clean PET bottles filled with water)
3/2	II	on	on	-	Contrast detection 18 % is activated. (e.g. clear glass bottles)
3/3		on	on	-	Contrast detection 40 % is activated. (e.g. coloured glass or non-transparent materials)

PEPPERL+FUCHS