



 ϵ





Model Number

OBG5000-R101-2EP-IO

Retroreflective sensor (glass) with fixed cable

Features

- Miniature design with versatile mounting options
- Detects transparent objects, i.e., clear glass, PET and transparent films
- Two machines in one: clear object detection or reflection operating mode with long range
- High degree of protection IP69K
- IO-link interface for service and process data


Product information

The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.


Dimensions




Electrical connection



Indicators/operating means





1	Teach-in button
2	Mode rotary switch
3	Operating indicator / dark on
4	Signal indicator
5	Operating indicator / light on

Ν	Normal mode
I	10 % contrast detection
Ш	18 % contrast detection
III	40 % contrast detection
L/D	Switching type
0	Keylock

Technical data General specifications Effective detection range 0 ... 3.5 m in TEACH mode; 0 ... 5 m at switch position "N" 0 ... 3.5 m in TEACH mode; 0 ... 5 m at switch position "N" Reflector distance 6 m Threshold detection range H85-2 reflector Reference target LFD Light source Light type modulated visible red light LED risk group labelling exempt group Diameter of the light spot approx. 170 mm at a distance of 3.5 m Angle of divergence approx. 5° Ambient light limit EN 60947-5-2 Functional safety related parameters 600 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Yellow I FD: Function indicator Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve Control elements Control elements 5-step rotary switch for operating modes selection 10 % - clean, water filled PET bottles Contrast detection levels 18 % - clear glass bottles 40 % - colored glass or opaque materials Adjustable via rotary switch **Electrical specifications** 10 ... 30 V DC Operating voltage U_{B} Ripple max. 10 % No-load supply current I₀ < 25 mA at 24 V supply voltage Protection class Interface Interface type IO-Link (via C/Q = BK) Transfer rate COM 2 (38.4 kBaud) 1.1 **IO-Link Revision** Min. cycle time 2.3 ms Process data input 2 Bit Process data witdh Process data output 2 Bit SIO mode support 0x110A01 (1116673) Device ID Compatible master port type Switching type The switching type of the sensor is adjustable. The default settina is C/Q - BK: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - WH: NPN normally closed / light-on, PNP normally open / Signal output 2 push-pull (4 in 1)outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category ≤ 1.5 V DC Voltage drop U_{d} 500 Hz Switching frequency Response time 1 ms Conformity IEC 61131-9 Communication interface Product standard EN 60947-5-2 **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) , movable cable not appropriate for conveyor chains -40 ... 70 °C (-40 ... 158 °F) Storage temperature **Mechanical specifications** Housing width 13.9 mm Housing height 33.8 mm Housing depth 18.3 mm Degree of protection IP67 / IP69 / IP69K Connection 2 m fixed cable Material Housing PC (Polycarbonate) Optical face РММА

Accessories

V31-WM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

V31-GM-2M-PUR

Female cordset, M8, 4-pin, PUR cable

IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

OMH-R101

Mounting Clamp

OMH-R101-Front

Mounting Clamp

OMH-4.1

Mounting Clamp

OMH-ML6

Mounting bracket

OMH-ML6-U

Mounting bracket

OMH-ML6-Z

Mounting bracket

OFR-100/100

Reflective tape 100 mm x 100 mm

REF-H33

Reflector with screw fixing

REF-H50

Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap

REF-H85-2

Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

REF-H32G-2

REF-ORR50G-2


Other suitable accessories can be found at www.pepperl-fuchs.com

> 267075-100065_eng.xml Date of issue: 2018-12-19 Release date: 2018-12-19 10:36

PEPPERL+FUCHS


Curves/Diagrams

UL approval



E87056, cULus Listed, class 2 power supply, type rating 1

Relative received light strength in switch position "N"



Settings

267075-100065_eng.xml

2018-12-19

Date of

2018-12-19 10:36

Release date:

Teach-in:

Use the rotary switch to select the required operating mode: Normal mode (N) or contrast level I - III.

To teach in a threshold or activate an operating mode, press the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s).

Release the "TI" button. Teach-in starts.

Successful teach-in is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs. The sensor will now operate in the selected operating mode with the taught-in threshold.

An unsuccessful teach-in is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs. After an unsuccessful teach-in, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Every taught-in switching threshold can be re-taught (overwritten) by pressing the "TI" button again.

Note: To ensure that the device functions reliably in Contrast mode, the device must be powered on at least 30 s before Teach-in.

Setting the Device to Maximum Sensitivity

Use the rotary switch to select the Normal mode (N) position.

Press the "TI" button for > 4 s. The yellow and green LEDs will go out.

Release the "TI" button.

The settings will be reset to maximum sensitivity. After successfully resetting, the yellow and green LEDs will flash alternately (2.5 Hz).

Switching between light on/dark on

Use the rotary switch to select the light on/dark on (L/D) position.

Press the "TI" button for > 1 s.

The respective operating indicator LED (L/D) will illuminate green and the switching type will change.

To reset the switching type, press the "TI" button for > 4 s.

The respective operating indicator LED (L/D) will illuminate green and the operating indicator will be reset to the most recently active switching



type.

Reset to Default Settings

Use the rotary switch to select the O position.

Press the "TI" button for > 10 s. The yellow and the green LEDs will both switch off.

Release the "TI" button. The yellow LED is on.

After resetting, the sensor will operate with the following default settings:

- Normal mode (N)
- Maximum sensitivity adjustment
- Dark on
- Pin 2 (white core): antivalent switching output

FPEPPERL+FUCHS