











# **Model Number**


#### RL28-55-LAS/47/82b/105

Retroreflective sensor with 5-pin, M12 x 1 plastic connector


## **Features**

- Visible red light, pulsed LASER light
- Ultra bright LEDs for power on, weak signal indication and switching state
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II
- Waterproof, degree of protection IP67

## **Dimensions**



# **Electrical connection**



- O = Light on
- = Dark on


## **Pinout**

dance with EN 60947-5-2



(brown) (white) (blue) BN WH BU BK GY (black)

# Indicators/operating means



Technical data		
General specifications		
Effective detection range		0 30 m
Reflector distance		0.3 30 m
Threshold detection range		42 m
Reference target		MH82 reflector
Light source		laser diode
Light type		modulated visible red light
Polarization filter		yes
Laser nominal ratings Note		LASER LIGHT , DO NOT STARE INTO BEAM
Laser class		1
Wave length		650 nm
Beam divergence		< 1.5 mrad
Pulse length		approx. 4.5 μs
Repetition rate		approx. 6 kHz 20 kHz
max. pulse energy		4 nJ
Diameter of the light spot		approx. 45 mm at 30 m
Angle of divergence  Ambient light limit		Emitter: < 0.1 ° Receiver: < 2 ° 50000 Lux
Functional safety related param	natare	30000 Lux
MTTF <sub>d</sub>	icicis	560 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green
Function indicator		2 LEDs yellow, light up when light beam is free, flash when falling short of the stability control, off when light beam is interrupted
Control elements		sensitivity adjustment (Adjustment to < 25% of the effective operating range) , Light-on/dark-on changeover switch
Electrical specifications		10 30 V DC
Operating voltage Ripple	U <sub>B</sub>	max. 10 %
No-load supply current	I <sub>0</sub>	≤ 35 mA
Protection class	.0	II, rated insulation voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1
Output		
Pre-fault indication output		1 PNP, inactive when falling short of the stability control for 10;s immediately inactive if 4 light beam interruptions take place
Switching type		light/dark on switchable
Signal output Switching voltage		2 PNP, complementary, short-circuit protected, reverse polarity protected , open collectors max. 30 V DC
Switching current		max. 200 mA
Voltage drop	U <sub>d</sub>	≤ 2.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Product standard		EN 60947-5-2
Laser safety		EN 60825-1
Ambient conditions		10 50 90 (14 100 95)
Ambient temperature Storage temperature		-10 50 °C (14 122 °F) -20 75 °C (-4 167 °F)
Mechanical specifications		-20 73 0 (-4 107 1)
Housing width		25.8 mm
Housing height		88 mm
Housing depth		54.3 mm
Degree of protection		IP67
Connection		5-pin, M12 x 1 plastic connector
Material		
Housing		Plastic ABS
Optical face Mass		Plastic pane 80 g
Approvals and certificates		00 g
Protection class		II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		E87056 , cULus Listed , class 2 power supply , type rating 1
FDA approval		IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

## **Accessories**

# **OMH-05**

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

### **OMH-07**

Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm

#### **OMH-21**

Mounting bracket

#### **OMH-22**

Mounting bracket

## OMH-MLV11-K

dove tail mounting clamp

#### **OMH-RLK29-HW**

Mounting bracket for rear wall mounting


#### OMH-RL28-C

Weld slag cover model


#### REF-MH82

Reflector with Micro-structure, rectangular 82 mm x 60 mm, mounting holes

Other suitable accessories can be found at www.pepperl-fuchs.com



# **Curves/Diagrams**



# Laser notice laser class 1

- The irradiation can lead to irritation especially in a dark environment. Do not point at people!
- Maintenance and repairs should only be carried out by authorized service personnel!
- Attach the device so that the warning is clearly visible and readable.
- Caution Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation
  exposure.